







由 Autodesk 教育版产品制作



性能:

额定电流: 2.0A
额定电压: 12V
耐电压: 500V
接触电阻: 30mΩ
绝缘电阻: 500MΩ
工作温度: -40℃~+85℃
塑件(材质): LCP
接触点(材质): 磷铜, 触点镀金3U",
使用寿命: 5000次以上



RECOMMENDED PCB LAYOUT TOP VIEW(. XX±0.05)

Pin数	PART NO.	DIM A	DIM B
2Pin	BC-27-2P230-B	4.0	2.0
3Pin	BC-27-3P230-B	6.0	4.0
4Pin	BC-27-4P230-B	8.0	6.0
5Pin	BC-27-5P230-B	10.0	8.0
6Pin	BC-27-6P230-B	12.0	10.0
7Pin	BC-27-7P230-B	14.0	12.0
8Pin	BC-27-8P230-B	16.0	14.0

版本REV.	更新标记REVISIONNOTE	日期DATE	未注公差 TOLERANCE
			X. XX ±0.35
			X.x ±0.25
			X.XX ±0.15
			X.XXX ±0.05
绘制DRAWN			视图方法 PROJECTION
设计DES'D			
审核CHK'D			
批准APPV'D			

JMECONN 东莞市文章济美电子有限公司	
品名ARTICLE: 电池连接器	
图号MODEL: BC-27-NP230-B	A4
比例SCALE:	单位UNIT: mm
页码SHEET: 共1页 第1页	