

Φ10.0mm NFC 3.0uH Antenna

FEATURES



- Operating Frequency: 13.56 MHz
- RF Power: 2W
- RoHS: Yes
- Operating Temperature: -40 to +85°C



PRODUCTS

Part No.	Weight	Dimensions (L x WxH)	Color
AINM002	0.05g	Φ 10x0.32mm	Golden

SPECIFICATIONS


PARAMETER	SPECIFICATION
Frequency Bands, MHz	13.56MHz
Nominal Impedance	50 Ω
Max Power (ambient temp of 25°C)	10 Watts
Color	Black
Storage Temperature Range (°C)	-40° C to +85° C
Operational Temperature Range (°C)	-40° C to +85° C
Material Substance Compliance	REACH/RoHS Compliant

MyAntenna RF Technology Co., Ltd


ADD:No.RM 410, Country Garden Phoenix Wisdom Valley, No. 50 Tiezai Road, Baoan District, Shenzhen, P.R.China.

TEL: +86-0755-86503881 FAX: +86-0755-27801677 E-mail: nfc@myantenna.com

ELECTRICAL DATA



HOUSING CONFIGURATIONS



Aboosty™ is owned by Shenzhen MyAntenna RF Technology Co., Ltd. (often abbreviated as MyAntenna).