





Cat. / Contato	Dimension					
	A	B	C	D	E	F
11	5,50	2,40	3,00	3,63	4,95	3,60
13	6,10	3,00	3,60	4,23	5,55	4,20
15	6,70	3,60	4,20	4,83	6,15	4,80
17	7,30	4,20	4,80	5,43	6,75	5,40
19	7,90	4,80	5,40	6,03	7,35	6,00
21	8,50	5,40	6,00	6,63	7,95	6,60
23	9,10	6,00	6,60	7,23	8,55	7,20
25	9,70	6,60	7,20	7,83	9,15	7,80
31	11,50	8,40	9,00	9,63	10,95	9,60
33	12,10	9,00	9,60	10,23	11,55	10,20
35	12,70	9,60	10,20	10,83	12,15	10,80
39	13,90	10,80	11,40	12,03	13,35	12,00
41	14,50	11,40	12,00	12,63	13,95	12,60
45	15,70	12,60	13,20	13,83	15,15	13,80
51	17,50	14,40	15,00	15,63	16,95	15,60



Scale 2:1
Long Cover type



3.3: Operating Temperature: $-55^{\circ}\text{C} \sim +85^{\circ}\text{C}$.



	深圳市虹成电子有限公司		品 名 TITLE		FPC座	
			料 号 PART NO		HC-FPC-0.3-39P-FHH10	
GENERAL TOLERANCES (UNLESS SPECIFIED)		比 例 SCALE	1 : 1			
X.X : ±0.30 X.X' : ±5°		单 位 UNIT	MM	制 图 DRAW	AhYe	
X.XX : ±0.20 X.XX' : ±2°		张 数 PART NO	1 OF 1	审 核 CHECKED	夏操云	
		版 本 REV	A	批 准 APPROVE	赵亮亮	