





Cat. Cont.	Dimension					
	A	B	C	D	E	F
11	5.50	2.40	3.00	3.63	4.95	3.60
13	6.10	3.00	3.60	4.23	5.55	4.20
15	6.70	3.60	4.20	4.83	6.15	4.80
17	7.30	4.20	4.80	5.43	6.75	5.40
19	7.90	4.80	5.40	6.03	7.35	6.00
21	8.50	5.40	6.00	6.63	7.95	6.60
23	9.10	6.00	6.60	7.23	8.55	7.20
25	9.70	6.60	7.20	7.83	9.15	7.80
31	11.50	8.40	9.00	9.63	10.95	9.60
33	12.10	9.00	9.60	10.23	11.55	10.20
35	12.70	9.60	10.20	10.83	12.15	10.80
39	13.90	10.80	11.40	12.03	13.35	12.00
41	14.50	11.40	12.00	12.63	13.95	12.60
45	15.70	12.60	13.20	13.83	15.15	13.80
51	17.50	14.40	15.00	15.63	16.95	15.60



Scale 2:1
Long Cover type



3.3: Operating Temperature: $-55^{\circ}\text{C} \sim +85^{\circ}\text{C}$.



	深圳市虹成电子有限公司		品 名	FPC座	
			TITLE		
			料 号	HC-FPC-0.3-51P-FHH10	
			PART NO		
GENERAL TOLERANCES (UNLESS SPECIFIED)		比 例 SCALE	1:1		
X.X :±0.30 X.X' :±5° X.XX :±0.20 X.XX':±2°		单 位 UNIT	MM	制 图 DRAW	AhYe
		张 数 PART NO	1 OF 1	审 核 CHECKED	夏操云
		版 本 REV	A	批 准 APPROVE	赵亮亮
					