


	REVISIONS				
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A	(A1)X1	尺寸修正, 图面升级整理图面	2025.1.4	阿树



PART NO.:

X1270 W R-2x22 A-9T V01
① ② ③ ④ ⑤ ⑥ ⑦

- ①Series No
②Category:W—Wafer
③Welding Board Angle:R—Stright 90°
④Row No.Pin No:2xXX—2x05~2x30Pin
⑤A:No gap
⑥Material:9T—PA9T UL94V—0
⑦Plating Category: V01—All Gold Flash

Specifications:

规格:

Voltage rating:250V AC/Min

额定电压: 250V AC/Min

Current rating:1A AC/DC

额定电流: 1A AC/DC

Withstanding voltage:500V AC/minute

耐受电压: 500V AC/分钟

Temperature range: -40°C $- +105^{\circ}\text{C}$


温度范围: $-40^{\circ}\text{C}-+105^{\circ}\text{C}$

Insulation resistance: $\geq 1000\text{M}\Omega$

绝缘电阻: $\geq 1000\text{M}\Omega$

Contact resistance: $\leq 20\text{m}\Omega$

PIN	A	B	C
2x03	2.54	8.71	10.11
2x04	3.81	9.98	11.38
2x05	5.08	11.25	12.65
2x07	7.62	13.79	15.19
2x08	8.89	15.06	16.46
2x09	10.16	16.33	17.73
2x10	11.43	17.60	19.00
2x12	13.97	20.14	21.54
2x13	15.24	21.41	22.81
2x15	17.78	23.95	25.35
2x17	20.32	26.49	27.89
2x20	24.13	30.30	31.70
2x22	26.67	32.84	34.24
2x25	30.48	36.65	38.05
2x30	36.83	43.00	44.40



PCB LAYOUT

AuGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERAUCES	

XK13 星城 Connection

XKB INDUSTRIAL PRECISION CO.,LIMITED

DESIGN	阿树	VIEW: 	MODEL TYPE: 1.27mm BTB Style Connectors		
CHECKED		UNIT: mm/in	PART NO.: X1270WR-2x22A-9TV01		
APPROVED		SIZE: A4	DWG NO.: X-X1270WR-2x22A-9TV01		
PRECISION CO., LIMITED			SCALE		
			PAGE		
			REVISION		
			N/A		
			1/1		
			A1		