




REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE		
A1	N/A		产品尺寸及料号变更，图面升级整理图面	2024.08.27	阿树




SPECIFICATIONS

Rated Current:1.0AMP
Contact Resistance:20mΩ Max
Withstand Voltage:500V AC/DC
Insulation Resistance:1000MΩ Min
Operation Temperature:-45°c~+125°c
Contact Material:Phosphor Brass
Contact Plating:Au or Sn Over Ni
Insulator Material:Polyester(UL94V-0)
Standard: PA6T
Max.Processing Temp: 230°C for 30-60 seconds
(260°C for 10 seconds)

PART NO.:

X1311 F R S-08-C43 D28
① ② ③ ④ ⑤ ⑥ ⑦

- ① Series No.
② Category:F-Female
③ Welding Board Angle:R-Stright 90°
④ Welding Way:S-SMT
⑤ Row No.Pin No:XX-01~40Pin
⑥ Plastic Height:C=4.3mm
⑦ Pin pitch:D=2.8mm



P.C.B Layout

ANGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:		MODEL TYPE:	1.27mm BTB Connector
CHECKED		UNIT:	mm/in	PART NO.:	X1311FRS-08-C43D28
APPROVED		SIZE:	A4	DWG NO.:	X-X1311FRS-08-C43D28

SCALE	PAGE	REVISION
N/A	1/1	A1