

1

2


3

4

| REVISIONS |         |          |             |            |
|-----------|---------|----------|-------------|------------|
| REV.      | ECN NO. | LOCATION | DESCRIPTION | DATE       |
| A1        | N/A     |          |             | 2025.12.22 |
| A2        | N/A     |          |             | 2026.03.09 |

## Specifications( )

- 1.Current rating( ):2.4A AC/DC
- 2.Withstanding voltage( ):≥1000V AC/minute
- 3.Insulation resistance( ):1000MΩ Min
- 4.Contact resistance( ):20mΩ Max
- 5.Temperature range( ):-40 -+105






3D VIEW

PART NO.:

X1273 W V S-16-9T SW BK

Series No  
Category:W-Wafer  
Welding Board Angle:V-Stright 180°  
Welding Way: S-SMT  
Row No.Pin No:XX-04~26Pin  
Material: 9T-Nylon 9T 94V-0  
Plating Category:SW-Bright Tin Plated  
Color: BK-Black;W-White

| X1273WVS-16-9TSWW                    | PA9T UL 94V-0 | WHITE       | BRASS                                        | TIN-PLATED       |
|--------------------------------------|---------------|-------------|----------------------------------------------|------------------|
| X1273WVS-16-9TSWBK                   |               | BLACK       |                                              |                  |
| PART NO.                             | MATERIAL      | COLOR       | MATERIAL(TERMINAL)                           | FINISH(TERMINAL) |
| DESIGN                               |               | VIEW:       | MODEL TYPE:<br>1.27mm Crimp Style Connectors |                  |
| CHECKED                              |               | UNIT: mm/in | PART NO.:<br>X1273WVS-16-9TSWBK              |                  |
| APPROVED                             |               | SIZE: A4    | DWG NO.:                                     |                  |
| XKB INDUSTRIAL PRECISION CO.,LIMITED |               |             | SCALE<br>N/A                                 | PAGE<br>1/1      |
|                                      |               |             | REVISION<br>A2                               |                  |



| NUMBER OF POSITIONS | DIM.A | DIM.B | DIM.C | DIM.D | NUMBER OF POSITIONS | DIM.A           | DIM.B | DIM.C | DIM.D | AuGLAR                 | ±5°   |
|---------------------|-------|-------|-------|-------|---------------------|-----------------|-------|-------|-------|------------------------|-------|
| 4                   | 8.86  | 6.35  | 3.81  | 7.66  | 16                  | 24.10           | 21.59 | 19.05 | 22.90 | X.                     | ±0.40 |
| 6                   | 11.40 | 8.89  | 6.35  | 10.20 | 18                  | 26.64           | 24.13 | 21.59 | 25.44 | X.x                    | ±0.30 |
| 8                   | 13.94 | 11.43 | 8.89  | 12.74 | 20                  | 29.18           | 26.67 | 24.13 | 27.98 | X.xx                   | ±0.20 |
| 10                  | 16.48 | 13.94 | 11.43 | 15.28 | 22                  | 31.72           | 29.21 | 26.67 | 30.52 | X.xxx                  | ±0.15 |
| 12                  | 19.02 | 16.51 | 13.97 | 17.82 | 24                  | 34.26           | 31.75 | 29.21 | 33.06 | UNSPECIFIED TOLERANCES |       |
| 14                  | 21.56 | 19.05 | 16.51 | 20.36 | 26                  | 36.80           | 34.29 | 31.75 | 35.60 |                        |       |
| www.helloxkb.com    |       |       |       |       |                     | www.helloxkb.cn |       |       |       | www.xk-dg.cn           |       |



XKB INDUSTRIAL PRECISION CO.,LIMITED