


REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A1	N/A			2025.12.22	
A2	N/A			2026.03.09	

Specifications()

- 1.Current rating():2.4A AC/DC
- 2.Withstanding voltage():≥1000V AC/minute
- 3.Insulation resistance():1000MΩ Min
- 4.Contact resistance():20mΩ Max
- 5.Temperature range():-40 -+105






3D VIEW

PART NO.:

X1273 W V S-06-9T SW BK

Series No
Category:W-Wafer
Welding Board Angle:V-Straight 180°
Welding Way: S-SMT
Row No.Pin No:XX-04~26Pin
Material: 9T-Nylon 9T 94V-0
Plating Category:SW-Bright Tin Plated
Color: BK-Black;W-White

X1273WVS-06-9TSWW	PA9T UL 94V-0	WHITE	BRASS	TIN-PLATED
X1273WVS-06-9TSWBK		BLACK		
PART NO.	MATERIAL	COLOR	MATERIAL(TERMINAL)	FINISH(TERMINAL)
DESIGN		VIEW:	MODEL TYPE: 1.27mm Crimp Style Connectors	
CHECKED		UNIT: mm/in	PART NO.: X1273WVS-06-9TSWBK	
APPROVED		SIZE: A4	DWG NO.:	
SCALE			PAGE	REVISION
N/A			1/1	A2



NUMBER OF POSITIONS	DIM.A	DIM.B	DIM.C	DIM.D	NUMBER OF POSITIONS	DIM.A	DIM.B	DIM.C	DIM.D	AuGLAR	±5°
4	8.86	6.35	3.81	7.66	16	24.10	21.59	19.05	22.90	X.	±0.40
6	11.40	8.89	6.35	10.20	18	26.64	24.13	21.59	25.44	X.x	±0.30
8	13.94	11.43	8.89	12.74	20	29.18	26.67	24.13	27.98	X.xx	±0.20
10	16.48	13.94	11.43	15.28	22	31.72	29.21	26.67	30.52	X.xxx	±0.15
12	19.02	16.51	13.97	17.82	24	34.26	31.75	29.21	33.06	UNSPECIFIED TOLERANCES	
14	21.56	19.05	16.51	20.36	26	36.80	34.29	31.75	35.60		

www.helloxkb.com

www.helloxkb.cn

www.xk-dg.cn



XKB INDUSTRIAL PRECISION CO.,LIMITED