

REVISONS				
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE
A1	N/A			2024.11.11
A2	N/A			2026.03.09

PART NO.:

X9127 W H-26 S1-PT RE

Series No
Category:W-Wafer
Welding Board Angle:H-Connect wires
Row No-Pin No:XX-04P~26P
Special No.:S1-With grooves and edges
Material:PT-PBT UL94V-0
Color: RD-purplish red
RE-Red Color

Poles	Dimensions(mm)	
	A	B
04	8.45	2.54
06	10.99	5.08
08	13.53	7.62
10	16.07	10.16
12	18.61	12.70
14	21.15	15.24
16	23.69	17.78
18	26.23	20.32
20	28.77	22.86
22	31.31	25.40
24	33.85	27.94
26	36.39	30.48

■ SPECIFICATIONS

- Voltage rating:500V AC/DC
- Current rating:1A AC/DC
- Withstanding Voltage:1000V AC/minute
- Temperature range:-40°C~+125°C
- Insulation resistance:≥1000MΩ
- Contact resistance ≤20mΩ
- After environment testing ≤30mΩ

X9127WH-26S1-PTRE	Red	PBT UL 94V-0	Brass	Tin-Plated
X9127WH-26S1-PTRD	purplish red			
PART NO	Color	Material	Material(Pin)	Finish(Pin)

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	VIEW:	UNIT: mm/in	SIZE: A4	MODEL TYPE: 1.27mm Crimp Style Connectors
CHECKED				PART NO.: X9127WH-26S1-PTRE
APPROVED				DWG NO.:

XKB INDUSTRIAL PRECISION CO.,LIMITED

SCALE	PAGE	REVISION
N/A	1/1	A2