







ROHS



NOTES:

1. SPECIFICATION:

- 1.1 CURRENT RATING: 1.0A MAX
- 1.2 VOLTAGE: 100 VAC
- 1.3 TEMPERATURE RANGE: -30 °C ~ 85 °C
- 1.4 CONTACT RESISTANCE: 30 MILLIONHM MAX
- 1.5 DIELECTRIC WITHSTANDING VOLTAGE: 200 VAC r.m.s
- 1.6 INSULATION RESISTNACE: 100 MEGOHMS MIN.




3	CONTACT	COPPER ALLOY T=0.15mm	Au/Ni Plated	1SET
2	HOUSING	High temperature plastic	BLACK	1PCS
1	SHELL	STAINLESS STEEL T=0.25mm	MATTE TIN/Ni Plated	1PCS
NO.	DESCRIPTION	MATERIAL	REMARKS	QTY

RECOMMENDED PCB LAYOUT
TOLERANCE:±0.05

COSTOMTER DRAWING		LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO.,LTD					
DRAWING							
CHECK							
APPROVAL							
TOLERANCES ARE		TITLE	MICRO-B连接器5PIN卧贴L5.0(直口)	REV.	A		
30-150	±0.35	PART NO.	LAIL-MICRO-B-5P-03-WT	UNITS	mm		
10-30	±0.2						
5-10	±0.15						
0-5	±0.1						
ANGLE		DWG.NO.		Projection			
±3°							

ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE



	REEL/TRAY	CARTON
CONNECTOR (PCS)	1400	14000

COSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO., LTD					
DRAWING							
CHECK							
APPROVAL							
TOLERANCES ARE		TITLE	MICRO-B连接器5PIN卧贴L5.0(直口)	REV.	A		
30-150	±0.35	PART NO.	LAIL-MICRO-B-5P-03-WT	UNITS	mm		
10-30	±0.2						
5-10	±0.15						
0-5	±0.1						
ANGLE		DWG.NO.				Projection	
±3°							