


ROHS




NOTE:

1.MATERIAL:

- a.HOUSING:PBT+GLASS FIBRE UL94 V-0 ;
PA66+GLASS FIBRE UL94 V-0
b.CONTACT:BRASS T=0.25±0.02mm
(SURFACE PLATING: Au SEE P/N +Sn80~100u"+Ni60u")
c.SHEEL: SPCC OR BRASS T=0.30±0.02mm
(SURFACE PLATING: Cu80u"~100u" Ni100u"~120u")

2.ELECTRIC:

- a.CONTACT RESISTANCE: 30 MILLIOHMS MAX
b.INSULATION RESISTANCE: 1000 MEGA OHMS MIN
c.DIELECTNIC VOLTAGE: 500V AC ONE SEC LEVEL
d.OPERATING TEMPERATURE: -25°C~ 85°C



PCB LAYOUT
PCB THICKNESS 1.60mm

COSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO., LTD			
DRAWING					
CHECK					
APPROVAL					
TOLERANCES ARE		TITLE	USB连接器Type-A 4PIN-侧插L19.5 (卷口)	REV.	A
30-150	±0.35	PART NO.	LAIL-TYPE-A-4P-01-CC	UNITS	mm
10-30	±0.2				
5-10	±0.15				
0-5	±0.1				
ANGLE		DWG.NO.		Projection	
±3°					