





RoHS

目錄
MAPX

设变内容
MODIFICATION

日期
DATE



RBCOMMENDBD P.C.B PATTBRN LAYD UT

电气特性:Electrical:

1. 额定电流: Current Rating
1.5A/contact terminal
2. 额定电压: Voltage Rating
30V DC
3. 接触阻抗:Contact Resistance
30 milliohms MAX
4. 耐电压:Dielectnic Withstanding Voitage:
500 V AC AT Sea Levot
5. 绝缘阻抗:Lnsulation Resistance:
1000MEGA ohms MIN

物理性能:Mechanical:

1. 插拔力: Cnnector Mate and Unmate Force
Mate force:3.57kgf (MAX)
Unmate force:0.7kgf (MIN)
2. 端子保持力: Terminal Retenion
1.0kgf (MIN)
3. 寿命: 1500次

原材料:Material:

1. 塑胶:Housing:pbt /lcp
2. 端子:Contact:Copper Alloy C2680
3. 外壳:Shell:SPCC/c2680

电镀:Finish:

1. 端子Contact: Au G/F u" Plated on contact area
Tin30u" Plated on solder area
Nickel 50u" Plated underplating over all.
2. 外壳Shell: Nickel 50u"Min plating over all.
3. Temperature Range:-55° C to +85° C

产品图

PRODUCT CHART DWG

公差一览表

TOLERANCE UNLESS OTHERWISE

Pin NUMBER	SIGNAL NAME
1	VBUS
2	D-
3	D+
4	GND

X	±0.35	X'	±5'
.X	±0.30	.X'	±2'
.XX	±0.25	.XX'	±1'
.XXX	±0.10	.XXX'	±0.5'

深圳市精拓金电子有限公司

单位 UNITS	MM	制图 DRAWING	L S S	产品料号 PRODUCT PART NO.	901-231A1021D10201
比例 SCALE	1:1	审核 CHKD	G Z F	产品名称 PRODUCT NO.	AF90度外扣直脚有边内弹 铁壳短弹T型PBT黑胶
日期 DATE	2021/03/10	核准 APPD	黄国荣	角法 VIEW	⊕ ⊖
				版本 VER	A0