

ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

SPECIFICATIONS

1)Electrical:





- 1.1 Contact Resistance: 30 M Ω Max
- 1.2 Insulation Resistance: 1000M Ω Min
- 1.3 Withstanding Voltage: 500V DC
- 1.4 Current rating 1.5AMP Max.
- 1.5 Total Mating Force: 35N Max.
- 1.6 Total Unmating force: 7N Min.
- 1.7temperature Rage: -25°C~+75°C

2)Material:

- 2.1 Housing: High temperature
Plastics UL94V-0 PBT Black ROHS
- 2.2 SHELL: SPCC
- 2.3 Contact: C2680

3)Finishing:

- 3.1 plating: Au or Sn Over 50u" Ni
- 3.2 Crimp Terminal :Gold-plating
- 3.3 Shell:Nickel-plating



PCB LAYOUT

COSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO.,LTD			
DRAWING					
CHECK					
APPROVAL					
TOLERANCES ARE		TITLE	USB连接器Type-A 4PIN-直插L13.7(卷口)	REV.	A
30-150	±0.35	PART NO.	LAIL-TYPE-A-4P-02-ZC	UNITS	mm
10-30	±0.2				
5-10	±0.15				
0-5	±0.1	DWG.NO.		Projection	