






ROHS



PCB LAYOUT

规格说明:Specifications:

电气特性:Electrical:

1. 额定电流: Current Rating
1.5A/contact terminal
2. 额定电压: Voltage Rating
30V DC
3. 接触阻抗:Contact Resistance
30 milliohms MAX
4. 耐电压:Dielectrcn Withstanding Voltage:
500 V AC AT Sea Level
5. 绝缘阻抗:Insulation Resistance:
1000MEGA ohms MIN

物理性能:Mechanical:

1. 插拔力: Cnector Mate and Unmate Force
Mate force:3.57kgf (MAX)
Unmate force:1.02kgf (MIN)
2. 端子保持力: Terminal Retenion
1.0kgf (MIN)

原材料:Material:

1. 塑胶:Housing:
Hing Temperature Tnermaplastics,
PBT White/Black
2. 端子:Contact:Copper Alloy C2680
Plated Gold in Mating Area;
Tin On Solder Talls
3. 外壳:Shell: Copper Alloy SPCC
Nickel Plating

5	SHELL-B	Fe	T=0.30	N i80- 100U"	1
4	SHELL-A	Fe	T=0.30	N i80- 100U"	1
3	TERMINAL-B	BRASS	T=0.25	Sn 80U"+ Au G/F"	4
2	TERMINAL-A	BRASS	T=0.25	Sn 80U"+ Au G/F"	4
1	HOUSING	PBT		BLACK	1
NO.	Part Name	MATERIAL	THICK	FINISH	Q'TY
CUSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司			
DRAWING		SHENZHEN LAILIAN ELECTRONICS CO.,LTD			
CHECK					
APPROVAL					
TOLERANCES ARE					
30-150	±0.35	ANGLE			
10-30	±0.2				
5-10	±0.15				
0-5	±0.1				
		±3°			
TITLE		TYPE-A连接器4PIN弯插L17.5 (2端口)		REV.	A
PART NO.		LAIL-TYPE-A-4PX2-02-WC		UNITS	mm
DWG.NO.				Projection	