







PCB Layout

TOLERANCE TABLE	
.0	±0.20
.00	±0.10
.000	±0.05

SPECIFICATION

Current Rate:3Amp

Contact Resistance:20mΩ MAX.at DC 1A

Insulation Resistance:1000MΩ MIN.atDC500V

Dielectirc Strength:AC500V PER minute

Operation Temperature:-40°to +105°

MATERIAL

Insulator:Polyester ,UL94V-0

Standard:PA6T

CONTACT:Brass

Contact plated: Gold Over Nickel

Poles:2~40P (Double)

Color:Black

Poles	PART NO.	Dimension mm	
		A	B
2*2	B-2200S04P-B120	2.54	5.48
2*3	B-2200S06P-B120	5.08	8.02
2*4	B-2200S08P-B120	7.62	10.56
2*5	B-2200S10P-B120	10.16	13.10
2*6	B-2200S12P-B120	12.70	15.64
2*7	B-2200S14P-B120	15.24	18.18
2*8	B-2200S16P-B120	17.78	20.72
2*9	B-2200S18P-B120	20.32	23.26
2*10	B-2200S20P-B120	22.86	25.80
...	...	...	...
2*40	B-2200S80P-B120	99.06	102.00

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKEMENG INDUSTRYCO., LTD			
CHECKED:	DATE:	TITLE: 220S-2*XP H=8.5MM Y型端子			
DRAWN: LYF	DATE: 2024-04-29	PART. NO.		B-2200SXXP-B120	
		UNIT	mm	SCALE	free
		FILE NO.		Ckmtw-220-00016	REV. A