





RoHS

目錄  
MAPX设变内容  
MODIFICATION日期  
DATE

## 电气特性:Electrical:

1. 额定电流: Current Rating  
1.5A/contact terminal
2. 额定电压: Voltage Rating  
30V DC
3. 接触阻抗: Contact Resistance  
30 milliohms MAX
4. 耐电压: Dielectric Withstanding Voltage:  
500 V AC AT Sea Level
5. 绝缘阻抗: Insulation Resistance:  
1000MEGA ohms MIN

## 物理性能: Mechanical:

1. 插拔力: Connector Mate and Unmate Force  
Mate force: 3.57kgf (MAX)  
Unmate force: 1.02kgf (MIN)
2. 端子保持力: Terminal Retention  
1.0kgf (MIN)
3. 寿命: 1500次

## 原材料: Material:

1. 塑胶: Housing: pbt /lcp
2. 端子: Contact: Copper Alloy C2680
3. 外壳: Shell: SPCC/c2680

## 电镀: Finish:

1. 端子 Contact: Au G/F u" Plated on contact area  
Tin50u" Plated on solder area  
Nickel 30u" Plated underplating over all.
2. 外壳 Shell: Nickel 50u" Min plating over all.
3. Temperature Range: -55° C to +85° C

| Pin NUMBER | SIGNAL NAME |
|------------|-------------|
| 1          | VBUS        |
| 2          | D-          |
| 3          | D+          |
| 4          | GND         |

## 产品图

PRODUCT CHART DWG

## 公差一览表

TOLERANCE UNLESS OTHERWISE

|      |       |       |       |
|------|-------|-------|-------|
| X.   | ±0.35 | X'.   | ±5°   |
| .X   | ±0.30 | .X'   | ±2°   |
| .XX  | ±0.25 | .XX'  | ±1°   |
| .XXX | ±0.10 | .XXX' | ±0.5° |

深圳市精拓金电子有限公司  
Shenzhen Jing Tuo Jin Electronics Co., Ltd.单位  
UNITS

MM

制图  
DRAWING

Erick

产品料号  
PRODUCT PART NO.

908-362A2021D10100

比例  
SCALE

1:1

审核  
CHKD

L S S

产品名称  
PRODUCT NO.

AF10.0A款四脚无边6.3铜壳LCP黑胶6.3DIP

日期  
DATE

2021/03/10

核准  
APPD

黄国荣

角法  
VIEW版本  
VER

A0