





ROHS



REV.	ECN NO.	DESCRIPTION	DRAW	DATE

规格说明:Specifications:

电气特性:Electrical:

- 额定电流: Current Rating
1.5A/contact terminal
- 额定电压: Voltage Rating
30V DC
- 接触阻抗:Contact Resistance
30 milliohms MAX
- 耐电压:Dielectric Withstanding Voitage:
500 V AC AT Sea Levol
- 绝缘阻抗:Lnsulation Resistance:
1000MEGA ohms MIN

物理性能:Mechanical:

- 插拔力: Cnnector Mate and Unmate Force
Mate force:3.57kgf (MAX)
Unmate force:1.02kgf (MIN)
- 端子保持力: Terminal Retenion
1.0kgf (MIN)

原材料:Matorial:

- 塑胶:Housing: PBT
- 端子:Contact:Copper Alloy C2680
- 外壳:Shell: SPCC

- 端子:Contact: Plated Gold in Mating Area;
Tin On Solder Talls
端子四周镀50U" (MIN) 锡, 半金锡1U"
- 外壳:Shell:
外四周镀80U" (MIN) 镍 Nickel Plating

COSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO.,LTD			
DRAWING					
CHECK					
APPROVAL					
TOLERANCES ARE		TITLE	TYPE-B连接器4PIN弯插L16.3 (平口)	REV.	A
30-150	±0.35	PART NO.	LAIL-TYPE-B-4P-01-WC	UNITS	mm
10-30	±0.2				
5-10	±0.15				
0-5	±0.1				
ANGLE		DWG.NO.		Projection	
±3°					