




RECOMMEND P.C.B LAYOUT
PCB TOLERANCE:±0.05 (TOP VIEW)



SPECIFICATIONS

Current Rating: 1.5 Amps
Insulation Resistance: 1000M Ω Min
Contact Resistance: 20m Ω Max
Withstanding Voltage: AC 500V
Operation Temperature: -40°to+105°
Contact Material: Brass
Standard: PA6T
Insulator Material: Polyester(UL 94V-0)
Contact Plating: Gold Flash
Max.Processing Temp: 240°C for30-60seconds
(260°C for 5 seconds)

P/N	PIN	DIM.A	DIM.B
BX-PM2.0-2-1PY	2*1	0.00	2.00
BX-PM2.0-2-2PY	2*2	2.00	4.00
BX-PM2.0-2-3PY	2*3	4.00	6.00
BX-PM2.0-2-4PY	2*4	6.00	8.00
BX-PM2.0-2-5PY	2*5	8.00	10.00
BX-PM2.0-2-6PY	2*6	10.00	12.00
BX-PM2.0-2-7PY	2*7	12.00	14.00
BX-PM2.0-2-8PY	2*8	14.00	16.00
BX-PM2.0-2-9PY	2*9	16.00	18.00
.....			
BX-PM2.0-2-40PY	2*40	(PIN-1)x2.0	(PIN)x2.0

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA			料号 PART NO.	BX-PM2.0-2-NPY		版本 REV.	A
			X.±0.30	X.°±5°	审核 CHECK	EVA			品名 TITLE	2.0FH H4.3 2xnPin 180μ W4.5 Uμ PC2.8 6T		页次 SHEET	1/1
			.X±0.20	.X°±1°	核准 APPROVAL	JADE			客户料号 CUTM.NO.				
			.XX±0.10	.XX°±0.5°	单位 UNITS	MM	比例 SCALE	1:1	 Bossie (博锡)				