




ROHS



Remarks:

Material:

1-1. Main Body: PBT, White

1-2. Terminal: Brass, T=0.25±0.01 (Surface Treatment: Overall Nickel Plating 40u", Tin Plating 80u" in Soldering Area, Gold Plating G/F in Contact Area)

1-3. Housing: Iron Material, T=0.30mm, Nickel Plating 30U" MIN

Electrical Performance:



2-1. Contact Resistance: 30 MILLIOHMS MAX

2-2. Insulation Resistance: 100 MEGA OHMS MIN

2-3. Withstand Voltage: 500V AC ONE MIN LEVEL

2-4. Operating Temperature: -25°C ~ 85°C

All materials used shall comply with RoHS standards.



PCB LAYOUT

COSTOMER DRAWING			 深圳市莱联电子有限公司			
DRAWING			SHENZHEN LAILIAN ELECTRONICS CO., LTD			
CHECK						
APPROVAL						
TOLERANCES ARE			TITLE	TYPE-A连接器4PIN弯插L14.5（卷口）	REV.	A
30-150	±0.35	ANGLE ±3°	PART NO.	LAIL-TYPE-A-4P-01-WC	UNITS	mm
10-30	±0.2		DWG.NO.			
5-10	±0.15					
0-5	±0.1					
			Projection			