





ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE




NOTE:

1.Electrical Performance:

- 1.1 Contact Resistance: 30 mΩ MAXIMUM
- 1.2 Rated Current: 1.5 A
- 1.3 Withstand Voltage: 500 V R.M.S.
- 1.4 Insulation: 1000 mΩ MIN
- 1.5 Operating Temperature: - 25°C ~ 85°C

2.Mechanical Performance:

- 2.1 Insertion Force: 3.57 kg MAX
- 2.2 Extraction Force: 1.02 kg MIN
- 2.3 Operating Cycles: 1500 CYCLES



RECOMMENDED PCBA LAYOUT
Top VIEW (TOLERANCE+±0.05)

COSTOMTER DRAWING			LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO., LTD				
DRAWING							
CHECK							
APPROVAL							
TOLERANCES ARE			TITLE	TYPE-A连接器4PINx2弯插L17.2（平口）	REV.	A	
30-150	±0.35	ANGLE	PART NO.	LAIL-TYPE-A-4PX2-01-WC	UNITS	mm	
10-30	±0.2						
5-10	±0.15						
0-5	±0.1						
			DWG.NO.		Projection		
±3°							