




ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

NOTE:
MATERIAL:
1.HOUSING: PBT UL94 V-0
2.CONTACT: BRASS T=0.25
(SURFACE PLATING: AuG/F+Sn80u”+Ni50u”)
3.SHEEL: SPCC OR BRASS T=0.30
(SURFACE PLATING: Cu80u+Ni80u”

SPECIFICATIONS:
1.CONTACT CURRENT RATING:1.5A MAX.
2.CONTACT RESISTANCE: 30 MΩ MAX.
3.WITHSTANDING VOLTAGE:500V AC MIN.
4.INSULATION RESISTANCE: 1000 MΩ MIN.




COSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO.,LTD				
DRAWING						
CHECK						
APPROVAL						
TOLERANCES ARE		TITLE	USB连接器Type-A 4PIN-侧插L19.4(直口)	REV.	A	
30-150	±0.35	PART NO.	LAIL-TYPE-A-4P-02-CC	UNITS	mm	
10-30	±0.2					
5-10	±0.15					
0-5	±0.1					
ANGLE		DWG.NO.		Projection		
±3°						

ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

- 包装注意事项:
- 1. 每15叠真空盘需用PE膜捆扎;
 - 2. 每箱需放入适量干燥剂;
 - 3. 产品标签按要求;
 - 4. 尾数箱请将内部多余的空间用干燥物填满,并在产品标签上标明尾数箱;

100	3000
PCS/真空盒	PCS/外箱



COSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO.,LTD				
DRAWING		TITLE USB连接器Type-A 4PIN-侧插L19.4(直口) REV. A				
CHECK						
APPROVAL						
TOLERANCES ARE		PART NO.	LAIL-TYPE-A-4P-02-CC	UNITS	mm	
30-150	±0.35					ANGLE
10-30	±0.2					
5-10	±0.15					
0-5	±0.1					
		DWG.NO.		Projection		