





标 记
MARKECN编号/变更内容
ECN NO/DEFINITION修 改
REVISE日 期
DATE核 准
APPROVEWhen Actuator Is Opened
Scale 2:1

Applicable FPC



Note:

1.Material



- 1.1: Housing: LCP Color: Natural
1.2: Actuator: LCP OR PA Color: Black
1.3: Contact: Phosphor Bronze.
1.4: LEG: Phosphor Bronze.

2.Plating

- 2.1: Contact: See Part Number.
2.2: LEG: Matte Tin Plating Over Nickel.

3.Rating:

- 3.1: Operating Voltage: 30V AC/DC.
3.2: Current Rating: 0.2A AC/DC.
3.3: Operating Temperature: $-55^\circ\text{C} \sim +85^\circ\text{C}$.

FPC/FFC Insert Direction
Recommended P.C.B Layout

2	端子	铜	点镀金	
1	底座	LCP	本色	
序号	品名	材质	电镀/颜色	备注

 深圳市虹成电子有限公司		品名 TITLE	FPC座	
		料号 PART NO	HC-FPC-0.3-39P-FH10	
GENERAL TOLERANCES (UNLESS SPECIFIED)		比列 SCALE	1:1	
X.X : ± 0.30	X.X' : $\pm 5^\circ$	单位 UNIT	MM	制图 DRAW
X.XX : ± 0.20	X.XX' : $\pm 2^\circ$	张数 PART NO	1 OF 1	审核 CHECKED
X.XXX : ± 0.10	X.XXX' : $\pm 1^\circ$	版本 REV	A	批准 APPROVE
				夏操云
				赵亮亮

