




Number of Contacts	Dimension				
	A	B	C	D	E
11	4.80	2.40	3.00	3.65	4.30
13	5.40	3.00	3.60	4.25	4.90
15	6.00	3.60	4.20	4.85	5.50
17	6.60	4.20	4.80	5.45	6.10
19	7.20	4.80	5.40	6.05	6.70
21	7.80	5.40	6.00	6.65	7.30
23	8.40	6.00	6.60	7.25	7.90
25	9.00	6.60	7.20	7.85	8.50
27	9.60	7.20	7.80	8.45	9.10
29	10.20	7.80	8.40	9.05	9.70
31	10.80	8.40	9.00	9.65	10.30
33	11.40	9.00	9.60	10.25	10.90
35	12.00	9.60	10.20	10.85	11.50
37	12.60	10.20	10.80	11.45	12.10
39	13.20	10.80	11.40	12.05	12.70
41	13.80	11.40	12.00	12.65	13.30
45	15.00	12.60	13.20	13.85	14.50
49	16.20	13.80	14.40	15.05	15.70
51	16.80	14.40	15.00	15.65	16.30



3.1: Operating Voltage: 30V AC/DC.
3.2: Current Rating: 0.2A AC/DC.
3.3: Operating Temperature: -55°C~+85°C.



FPC/FFC Insert Direction
Recommended P.C.B Layout 

	深圳市虹成电子有限公司			品 名	FPC座	
				TITLE		
				料 号	HC-FPC-0.3-15P-FH10	
				PART NO		
GENERAL TOLERANCES (UNLESS SPECIFIED)			比 列 SCALE	1 : 1		
X.X ±0.30 X.X* ±5*			单 位 UNIT	MM	制 图 DRAW	AhYe
X.XX ±0.20 X.XX* ±2*			张 数 PART NO	1 OF 1	审 核 CHECKED	夏操云
X.XXX±0.10 X.XXX* ±1*			版 本 REV	A	批 准 APPROVE	赵亮亮
						