

NOTE:

1. MATERIAL:
HOUSING:LCP, COLOR: NATURAL.
CONTACTS: COPPER ALLOY: Au, 0.025 um MIN. Ni 1,0 um MIN
PEG: COPPER ALLOY: Sn 2,0 um MIN. Ni 1,0 um MIN
ACTUATOR:LCP OR PA . COLOR:BLACK
2. RATING:
OPERATING VOLTAGE: 50Vrms AC.
CURRENT RATING: 0.5A.
OPERATING TEMPERATURE: 55°C~+85°C.
OPERATING HUMIDITY RANGE: RELATIVE HUMIDITY 90% MAX.(NO CONDENSATION)
STORAGE TEMPERATURE RANGE: -10°C~+50°C.
STORAGE HUMIDITY RANGE: RELATIVE HUMIDITY 90% MAX.(NO CONDENSATION)

<http://hcdz2017.com/>