







REVISION			
LTR	DESCRIPTION	DATE	APP
A0	NEW RELEASE	05/20/2020	PECK

P.C.B LAYOUT



⑪	SPRING COIL	1	WIRE	
⑩	CLIP PIECE	1	Phosphor Copper	MB: Ag PLATED
⑨	SWITCH TERMINAL	1	Brass	MB: Ag PLATED
⑧	SWITCH COVER	1	PA66	BLACK
⑦	SWITCH KNOB	1	POM	BLACK
⑥	SWITCH HOUSING	1	PBT(UL 94V-0)	BLACK
⑤	HOUSING	1	PBT(UL 94V-0)	BLACK
④	AXIS SUPPORT	1	Brass	MB: Ni Sn PLATED
③	3# CONTACT FOOT	1	Phosphor Copper	MB: Ag PLATED
②	2# CONTACT FOOT	1	Brass	MB: Ag PLATED
①	1# CONTACT FOOT	1	Brass	MB: Ag PLATED
NO.	PART NAME	Q'TY	MATERIAL	REMARK

LEVEL		A[better product]		B[average product]	
PROJECT					
Electrical Properties	Contact Rating	0.5A, 24V DC			
	Initial Contact Resistance	50mΩ max.			
	Insulation Resistance	100MΩ min.500V DC	Skey/PD: 100MΩ min.300V DC		
	Withstand Voltage	500V AC for 1 minute	350 V AC for 1 minut		
Durable Performance	There No Load	6,000 Cycles	5,000 Cycles		
	Rated Load	5,000 Cycles	4,000 Cycles		
Storage temp.		-35℃~+75℃(Operating Temp:)			
Operating Force		IF:10~20N MAX. (EF:10.0N MIN.)			
Heat Rrsistance		IR Reflow:255℃, 5sec. Manual :350℃, 3sec.			

DIMENSION CLASSIFICATION	
■	CRITICAL
☒	MAJOR

TOLERANCE TABLE

.X	±	0.40
.XX	±	0.25
.XXX	±	0.10
ANGLE	±	2°

台灣碩方精密電子科技有限公司
TAIWAN SOFNG PRECISION ELECTRONIC CO., LTD

TITLE PJ-306B 卧插式3.5耳机
插座-5+8PIN加长型

PART NO. PJ-306B

APPROVED Peck DWG NO. SOF-G006

CHECKED Paul SCALE 1:1 UNIT mm SIZE A4

DRAWIN David REV AO SHEET NO. 1/1



開關, 连接器
SOFNG