


[illegible]

RECOMMENDED PCB LAYOUT

Note:

- 1: Material(材料) :

Housing: PA46+30%GF (胶芯: PA46)

Pin: Brass C3604 (针体: 黄铜 C3604)

- 2: Plating(电镀) :

Pin: 3u' Au over 50~80u' Ni

针体：镀金3u'，镍底50~80u'。

- 3: Electrical(电气特性):

Insulation Resistance: 1,000M Ω minimum.

(绝缘电阻: 1,000MΩ 以上)


Dielectric Withstand Voltage: 500VAC/minute.

(抗击电压: 500VAC/minute)

- 4: WorkTemperture(工作环境):

Withstanding Higt Temperature: 280°C

Operational Temperature: $-40^{\circ}\text{C} \sim +85^{\circ}\text{C}$



深圳市鑫扬泽电子有限公司

HTTP://WWW.XYZPOGOPIN.COM

TEL:0755-28773277 FAX:0755-28891353



SCALE:	N/A	UNIT	mm
SHEET:	1 of 1	PROJECTION	
DATE:	2014.11.11	VER.	D.0

THE UNMARKED TOLERANCE ARE AS BELOW :

LENGTH

ANGLE

REFERENCES

TABLE 1

X.XX	±0.05mm
Y.Y	±0.10mm

X.XX	±0.50°
Y.Y	±1.00°

DESIGNED BY:		DWG. NO.	YZ65815040T-04025-01
CHECKED BY:		TITLE:	Pogo pin连接器
APPROVED BY:			