
DLL® 德利来 Connectors

# 43025/43045/43020

3.00mm Pitch Wire To Board And Wire To Wire Connector




## 技术特性/Specifications:


额定电压 Rated voltage: 250V AC, DC
额定电流 Rated current: 3.5A AC,DC
接触电阻 Contact resistance: 20mΩ max
绝缘电阻 Insulation resistance: 1000MΩ min
耐压 Withstand volage: 1000V AC/minute
环境温度 Ambient temperature:-40℃～+105℃
适用线规 Wire range: AWG#32～#28


IATF16949 ISO9001 ISO14001 REACH ROHS SONY Green Partner CE


电话/TEL：+86-577-62213798
传真/FAX：+86-577-62122577
http://www.zjdll.com


| REV. | REVISION DESCRIPTION | DATE | APPD |
|---|---|---|---|
| | | | |







# NOTES

Available in 02 through 24 Circuits.

Mates with DL30001-Y Series Housing.

Material : LCP UL94V-0.

Pin Material : Brass.Tin-plated .




PCB LAYOUT

| 序号 | 图号 | 名称 | 材料 | 数量 | 附件 |
|---|---|---|---|---|---|
| 3 | ③ | 基座 | LCP | 1 | UL94V-0 |
| 2 | ② | 焊片 | 黄铜 | 2 | 镀锡 |
| 1 | ① | 接触件 | 黄铜 | N* | 镀锡 |

| Circuits | Product name | Dimension mm | | Circuits | Product name | Dimension mm | |
|---|---|---|---|---|---|---|---|
| | | A | B | | | A | B |
| 2x1 | 43045-2AB | -- | 6.60 | 2x7 | 43045-14AB | 18.00 | 24.60 |
| 2x2 | 43045-4AB | 3.00 | 9.60 | 2x8 | 43045-16AB | 21.00 | 27.60 |
| 2x3 | 43045-6AB | 6.00 | 12.60 | 2x9 | 43045-18AB | 24.00 | 30.60 |
| 2x4 | 43045-8AB | 9.00 | 15.60 | 2x10 | 43045-20AB | 27.00 | 33.60 |
| 2x5 | 43045-10AB | 12.00 | 18.60 | 2x11 | 43045-22AB | 30.00 | 36.60 |
| 2x6 | 43045-12AB | 15.00 | 21.60 | 2x12 | 43045-24AB | 33.00 | 39.60 |

| GENERAL TOLERANCES (UNLESS SPECIFIED) | | ZHE JIANG DELI CONNECTORS CO .,LTD | | |
|---|---|---|---|---|
| .X: ± 0.25 | X° : ± 3.0° | PRODUCT NAME: DL30003(43045)-AB | TITLE: 3.0 mm Pitch Wire To Board SMT Wafer | |
| .XX: ± 0.15 | .X° : ± 2.0° | | | |
| .XXX: ± 0.01 | .XX° : ± 1.0° | DR:Chen Quan Long | DATE:20/07/27 | PART NO: |
| FINISH: | | CHKD:Wu Hui | DATE:20/07/27 | SCALE: N/A PAGE: 1/1 |
| DRAWING NO: | | APPD:Ren An De | DATE:20/07/27 | UNITS: mm REV.: A |

| REV. | REVISION DESCRIPTION | DATE | APPD |
|---|---|---|---|
| | | | |


# NOTES


Available in 02 through 24 Circuits.


Mates with DL30001-Y Series Housing.


Material : LCP  UL94V-0.


Pin Material : Brass.Tin-plated .








| 3 | ③ | 基座 | LCP | 1 | UL94V-0 |
|---|---|---|---|---|---|
| 2 | ② | 焊片 | 黄铜 | 2 | 镀锡 |
| 1 | ① | 接触件 | 黄铜 | N* | 镀锡 |
| 序号 | 图号 | 名称 | 材料 | 数量 | 附件 |


| Circuits | Product name | Dimension mm | | Circuits | Product name | Dimension mm | |
|---|---|---|---|---|---|---|---|
| | | A | B | | | A | B |
| 2x1 | 43045-2AWB | -- | 6.60 | 2x7 | 43045-14AWB | 18.00 | 24.60 |
| 2x2 | 43045-4AWB | 3.00 | 9.60 | 2x8 | 43045-16AWB | 21.00 | 27.60 |
| 2x3 | 43045-6AWB | 6.00 | 12.60 | 2x9 | 43045-18AWB | 24.00 | 30.60 |
| 2x4 | 43045-8AWB | 9.00 | 15.60 | 2x10 | 43045-20AWB | 27.00 | 33.60 |
| 2x5 | 43045-10AWB | 12.00 | 18.60 | 2x11 | 43045-22AWB | 30.00 | 36.60 |
| 2x6 | 43045-12AWB | 15.00 | 21.60 | 2x12 | 43045-24AWB | 33.00 | 39.60 |

| GENERAL TOLERANCES (UNLESS SPECIFIED) | | ZHE JIANG DELI CONNECTORS CO .,LTD | | |
|---|---|---|---|---|
| .X: ± 0.25 | X° : ± 3.0° | PRODUCT NAME: DL30003(43045)-AWB | | TITLE: 3.0 mm Pitch Wire To Board SMT Wafer |
| .XX: ± 0.15 | .X° : ± 2.0° | | | |
| .XXX: ± 0.01 | .XX° : ± 1.0° | DR:Chen Quan Long | DATE:20/07/27 | PART NO: |
| FINISH: | | CHKD:Wu Hui | DATE:20/07/27 | SCALE: N/A / PAGE: 1/1 |
| DRAWING NO: | | APPD:Ren An De | DATE:20/07/27 | UNITS: mm / REV.: A |

| REV. | REVISION DESCRIPTION | DATE |
|---|---|---|
| | | |








## NORES:

1. Rated voltage: 250V AC.DC
2. Rated current: 3.5A AC DC
3. Contact resistance: ≤20 mΩ
4. lnsulation resistance: ≥1000 mΩ
5. Withstand voltage: 1000V AC/minute
6. Ambient temprature:-40℃～105℃
7. Materials:Nylon UL94V-0(2)
8. Matched RoHS criteria

| Circuits | TYPE | Dimension mm | |
|---|---|---|---|
| | | A | B |
| 2X1 | 43045-2A | - | 6.6 |
| 2X2 | 43045-4A | 3.0 | 9.6 |
| 2X3 | 43045-6A | 6.0 | 12.6 |
| 2X4 | 43045-8A | 9.0 | 15.6 |
| 2X5 | 43045-10A | 12.0 | 18.6 |
| 2X6 | 43045-12A | 15.0 | 21.6 |
| 2X7 | 43045-14A | 18.0 | 24.6 |
| 2X8 | 43045-16A | 21.0 | 27.6 |
| 2X9 | 43045-18A | 24.0 | 30.6 |
| 2X10 | 43045-20A | 27.0 | 33.6 |
| 2X11 | 43045-22A | 30.0 | 36.6 |
| 2X12 | 43045-24A | 33.0 | 39.6 |






2A 4-24A


PCB LAYOUT

| GENERAL TOLERANCES (UNLESS SPECIFIED) | | ZHE JIANG DELI CONNECTORS CO .,LTD | | |
|---|---|---|---|---|
| .X: ± 0.25 | X° : ± 3.0° | PRODUCT NAME: DL30003(43045)-A | | TITLE: 3.0 mm Pitch Wire To Board Wafer |
| .XX: ± 0.15 | .X° : ± 2.0° | | | |
| .XXX:± 0.01 | .XX° :± 1.0° | DR:Chen Quan Long | DATE:20/04/03 | PART NO: |
| FINISH: | | CHKD: Wu Hui | DATE:20/04/03 | SCALE: N/A PAGE: 1/1 |
| DRAWING NO: | | APPD:Ren An De | DATE:20/04/03 | UNITS: mm REV.: B |

| REV. | REVISION DESCRIPTION | DATE |
|---|---|---|
| | | |









## NOTES:

1. Rated voltage: 250V AC.DC
2. Rated current: 3.5A AC DC
3. Contact resistance: ≤20 mΩ
4. Insulation resistance: ≥1000 mΩ
5. Withstand voltage: 1000V AC/minute
6. Ambient temprature:-40℃～105℃
7. Materials:Nylon UL94V-0(2)
8. Matched RoHS criteria










PCB LAYOUT

| GENERAL TOLERANCES (UNLESS SPECIFIED) | | ZHE JIANG DELI CONNECTORS CO .,LTD | | |
|---|---|---|---|---|
| .X: ± 0.25 | X° : ± 3.0° | PRODUCT NAME: 43045-6A-YZDZ | | TITLE: 3.0 mm Pitch Wire To Board Wafer |
| .XX: ± 0.15 | .X° : ± 2.0° | | | |
| .XXX: ± 0.01 | .XX° : ± 1.0° | DR:Yuan Jun Rong | DATE:20/04/03 | PART NO: |
| FINISH: | | CHKD: Wu Hui | DATE:20/04/03 | SCALE: N/A / PAGE: 1/1 |
| DRAWING NO: | | APPD:Ren An De | DATE:20/04/03 | UNITS: mm / REV.: A |

| REV. | REVISION DESCRIPTION | DATE |
|---|---|---|
| | | |








## NOTES:

1. Rated voltage: 250V AC.DC
2. Rated current: 3.5A AC DC
3. Contact resistance: ≤20 mΩ
4. Insulation resistance: ≥1000 mΩ
5. Withstand voltage: 1000V AC/minute
6. Ambient temprature:-40℃～105℃
7. Materials:Nylon UL94V-0(2)
8. Matched RoHS criteria










PCB LAYOUT

| GENERAL TOLERANCES (UNLESS SPECIFIED) | | ZHE JIANG DELI CONNECTORS CO .,LTD | | |
|---|---|---|---|---|
| .X: ± 0.25 | X° : ± 3.0° | PRODUCT NAME: 43045-6A-DZ | | TITLE: 3.0 mm Pitch Wire To Board Wafer |
| .XX: ± 0.15 | .X° : ± 2.0° | | | |
| .XXX:± 0.01 | .XX° :± 1.0° | DR:Yuan Jun Rong | DATE:20/04/03 | PART NO: |
| FINISH: | | CHKD: Wu Hui | DATE:20/04/03 | SCALE: N/A / PAGE: 1/1 |
| DRAWING NO: | | APPD:Ren An De | DATE:20/04/03 | UNITS: mm / REV.: B |

| REV. | REVISION DESCRIPTION | DATE |
|---|---|---|
| | | |









# NOTES:

1、Rated voltage: 250V AC.DC
2、Rated current: 3.5A AC.DC
3、Contact resistance : ≤20mΩ
4、Insulation resistance : ≥1000MΩ
5、Withstand voltage : 1000V AC/minute
6、Ambient temperature : -40℃～105℃
7、Materials : Nylon UL94V-0(2)
8、Green Material RoHS Compliant


| Circuits | Product name | Dimension mm | | |
|---|---|---|---|---|
| | | A | B | C |
| 2X1 | 43045-2AWS | - | 6.6 | - |
| 2X2 | 43045-4AWS | 3.0 | 9.6 | - |
| 2X3 | 43045-6AWS | 6.0 | 12.6 | - |
| 2X4 | 43045-8AWS | 9.0 | 15.6 | 4.7 |
| 2X5 | 43045-10AWS | 12.0 | 18.6 | 7.7 |
| 2X6 | 43045-12AWS | 15.0 | 21.6 | 10.7 |
| 2X7 | 43045-14AWS | 18.0 | 24.6 | 13.7 |
| 2X8 | 43045-16AWS | 21.0 | 27.6 | 16.7 |
| 2X9 | 43045-18AWS | 24.0 | 30.6 | 19.7 |
| 2X10 | 43045-20AWS | 27.0 | 33.6 | 22.7 |
| 2X11 | 43045-22AWS | 30.0 | 36.6 | 25.7 |
| 2X12 | 43045-24AWS | 33.0 | 39.6 | 28.7 |




2AWS





4AWS




6AWS


PCB LAYOUT






8-24AWS


| GENERAL TOLERANCES (UNLESS SPECIFIED) | | ZHE JIANG DELI CONNECTORS CO .,LTD | | |
|---|---|---|---|---|
| .X: ± 0.25 | X° : ± 3.0° | PRODUCT NAME: DL30003(43045)-AWS | | TITLE: 3.0 mm Pitch Wire To Board Wafer |
| .XX: ± 0.15 | .X° : ± 2.0° | | | |
| .XXX:± 0.01 | .XX° :± 1.0° | DR:Chen Quan Long | DATE:20/04/03 | PART NO: |
| FINISH: | | CHKD: Wu Hui | DATE:20/04/03 | SCALE: N/A / PAGE: 1/1 |
| DRAWING NO: | | APPD:Ren An De | DATE:20/04/03 | UNITS: mm / REV.: B |

| REV. | REVISION DESCRIPTION | DATE |
|---|---|---|
| | | |




4AWS


PCB 安装尺寸


# NOTES:


1、Rated voltage: 250V AC.DC
2、Rated current: 3.5A AC.DC
3、Contact resistance : ≤20mΩ
4、Insulation resistance : ≥1000MΩ
5、Withstand voltage : 1000V AC/minute
6、Ambient temperature : -40℃～105℃
7、Materials : Nylon UL94V-0(2)
8、Green Material RoHS Compliant

| GENERAL TOLERANCES (UNLESS SPECIFIED) | | ZHE JIANG DELI CONNECTORS CO .,LTD | | |
|---|---|---|---|---|
| .X: ± 0.25 | X° : ± 3.0° | PRODUCT NAME: DL30003(43045)-4AWS-02 | | TITLE: 3.0 mm Pitch Wire To Board Wafer |
| .XX: ± 0.15 | .X° : ± 2.0° | | | |
| .XXX:± 0.01 | .XX° :± 1.0° | DR:Chen Quan Long | DATE:20/04/03 | PART NO: |
| FINISH: | | CHKD: Wu Hui | DATE:20/04/03 | SCALE: N/A / PAGE: 1/1 |
| DRAWING NO: | | APPD:Ren An De | DATE:20/04/03 | UNITS: mm / REV.: B |

| REV. | REVISION DESCRIPTION | DATE |
|---|---|---|
| | | |








## NOTES:

1. Rated voltage: 250V AC.DC
2. Rated current: 3.5A AC DC
3. Contact resistance: ≤20 mΩ
4. lnsulation resistance: ≥1000 mΩ
5. Withstand voltage: 1000V AC/minute
6. Ambient temprature:-40℃～105℃
7. Materials:Nylon UL94V-0(2)
8. Matched RoHS criteria





PCB LAYOUT

| GENERAL TOLERANCES (UNLESS SPECIFIED) | | ZHE JIANG DELI CONNECTORS CO .,LTD | | | |
|---|---|---|---|---|---|
| .X: ± 0.25 | X° : ± 3.0° | PRODUCT NAME: 43045-6AWS-DZ | | TITLE: 3.0 mm Pitch Wire To Board Wafer | |
| .XX: ± 0.15 | .X° : ± 2.0° | | | | |
| .XXX:± 0.01 | .XX° :± 1.0° | DR:Yuan Jun Rong | DATE:20/04/03 | PART NO: | |
| FINISH: | | CHKD: Wu Hui | DATE:20/04/03 | SCALE: N/A | PAGE: 1/1 |
| DRAWING NO: | | APPD:Ren An De | DATE:20/04/03 | UNITS: mm | REV.: B |

| REV. | REVISION DESCRIPTION | DATE | APPD |
|---|---|---|---|
| | | | |





## NOTES

Available in 02 through 24 Circuits.

Mates with DL30001/DL30003 series housing.

Material : Nylon UL94V-0(2).


Accepts DL30001-T Crimp Terminal.




| Circuits | PRODUCT NAME | Dimension mm | | Circuits | PRODUCT NAME | Dimension mm | |
|---|---|---|---|---|---|---|---|
| | | A | B | | | A | B |
| 2X1 | 43025-2Y | – | 3.90 | 2X7 | 43025-14Y | 18.00 | 21.90 |
| 2X2 | 43025-4Y | 3.00 | 6.90 | 2X8 | 43025-16Y | 21.00 | 24.90 |
| 2X3 | 43025-6Y | 6.00 | 9.90 | 2X9 | 43025-18Y | 24.00 | 27.90 |
| 2X4 | 43025-8Y | 9.00 | 12.90 | 2X10 | 43025-20Y | 27.00 | 30.90 |
| 2X5 | 43025-10Y | 12.00 | 15.90 | 2X11 | 43025-22Y | 30.00 | 33.90 |
| 2X6 | 43025-12Y | 15.00 | 18.90 | 2X12 | 43025-24Y | 33.00 | 36.90 |

| GENERAL TOLERANCES (UNLESS SPECIFIED) | | ZHE JIANG DELI CONNECTORS CO .,LTD | | |
|---|---|---|---|---|
| .X: ± 0.25 | X° : ± 3.0° | PRODUCT NAME: DL30001(43025)-Y | | TITLE: 3.0mm Pitch Housing |
| .XX: ± 0.15 | .X° : ± 2.0° | DR:Chen Quan Long | DATE:20/08/01 | PART NO: |
| .XXX: ± 0.01 | .XX° : ± 1.0° | CHKD: Wu Hui | DATE:20/08/01 | SCALE: N/A / PAGE: 1/1 |
| FINISH: | | APPD:Ren An De | DATE:20/08/01 | UNITS: mm / REV.: A |
| DRAWING NO: | | | | |

| REV. | REVISION DESCRIPTION | DATE | APPD |
|---|---|---|---|
| | | | |





## NOTES


Available in 02 through 24 Circuits.

Mates with DL30001-Y Series Housing.

Material : Nylon  UL94V-0 (2).

Accepts DL30001-RT Crimp Terminal.








安装尺寸

| Circuits | TYPE | Dimension mm | | | |
|---|---|---|---|---|---|
| | | A | B | C | D |
| 2X1 | 43020-2R | - | 3.90 | 4.21 | 7.90 |
| 2X2 | 43020-4R | 3.00 | 6.90 | 7.21 | 10.90 |
| 2X3 | 43020-6R | 6.00 | 9.90 | 10.21 | 13.90 |
| 2X4 | 43020-8R | 9.00 | 12.90 | 13.21 | 16.90 |
| 2X5 | 43020-10R | 12.00 | 15.90 | 16.21 | 19.90 |
| 2X6 | 43020-12R | 15.00 | 18.90 | 19.21 | 22.90 |
| 2X7 | 43020-14R | 18.00 | 21.90 | 22.21 | 25.90 |
| 2X8 | 43020-16R | 21.00 | 24.90 | 25.21 | 28.90 |
| 2X9 | 43020-18R | 24.00 | 27.90 | 28.21 | 31.90 |
| 2X10 | 43020-20R | 27.00 | 30.90 | 31.21 | 34.90 |
| 2X11 | 43020-22R | 30.00 | 33.90 | 34.21 | 37.90 |
| 2X12 | 43020-24R | 33.00 | 36.90 | 37.21 | 40.90 |

| GENERAL TOLERANCES (UNLESS SPECIFIED) | | ZHE JIANG DELI CONNECTORS CO .,LTD | | |
|---|---|---|---|---|
| .X: ± 0.25 | X° : ± 3.0° | PRODUCT NAME: DL30001(43020)-R | | TITLE: 3.0mm Pitch Wire To Wire Plug Housing |
| .XX: ± 0.15 | .X° : ± 2.0° | | | |
| .XXX: ± 0.01 | .XX° : ± 1.0° | DR:Chen Quan Long | DATE:20/08/01 | PART NO: |
| FINISH: | | CHKD: Wu Hui | DATE:20/08/01 | SCALE: N/A / PAGE: 1/2 |
| DRAWING NO: | | APPD:Ren An De | DATE:20/08/01 | UNITS: mm / REV.: A |

| REV. | REVISION DESCRIPTION | DATE | APPD |
|---|---|---|---|
| | | | |





## NOTES

Available in 02 through 24 Circuits.

Mates with DL30001-Y Series Housing.

Material : Nylon UL94V-0 (2) .


Accepts DL30001-RT Crimp Terminal.




| Circuits | TYPE | Dimension mm | |
|---|---|---|---|
| | | A | B |
| 2X1 | 43020-2RF | - | 3.90 |
| 2X2 | 43020-4RF | 3.00 | 6.90 |
| 2X3 | 43020-6RF | 6.00 | 9.90 |
| 2X4 | 43020-8RF | 9.00 | 12.90 |
| 2X5 | 43020-10RF | 12.00 | 15.90 |
| 2X6 | 43020-12RF | 15.00 | 18.90 |
| 2X7 | 43020-14RF | 18.00 | 21.90 |
| 2X8 | 43020-16RF | 21.00 | 24.90 |
| 2X9 | 43020-18RF | 24.00 | 27.90 |
| 2X10 | 43020-20RF | 27.00 | 30.90 |
| 2X11 | 43020-22RF | 30.00 | 33.90 |
| 2X12 | 43020-24RF | 33.00 | 36.90 |

| GENERAL TOLERANCES (UNLESS SPECIFIED) | | ZHE JIANG DELI CONNECTORS CO .,LTD | | |
|---|---|---|---|---|
| .X: ± 0.25 | X° : ± 3.0° | PRODUCT NAME: DL30001(43020)-RF | | TITLE: 3.0mm Pitch Wire To Wire Plug Housing |
| .XX: ± 0.15 | .X° : ± 2.0° | | | |
| .XXX: ± 0.01 | .XX° : ± 1.0° | DR:Yuan Jun Rong | DATE:20/08/01 | PART NO: |
| FINISH: | | CHKD: Wu Hui | DATE:20/08/01 | SCALE: N/A / PAGE: 1/2 |
| DRAWING NO: | | APPD:Ren An De | DATE:20/08/01 | UNITS: mm / REV.: A |

| REV. | REVISION DESCRIPTION | DATE | APPD |
|---|---|---|---|
| | | | |




# NOTES

Used in DL30001-Y Series Housing.


Accepts AWG #28～20 Wire Range.

Material : Phosphor Bronze .


Finish: Tin plated.

Thickness: 0.2 mm.


Green Material RoHS Compliant.




SECTION A-A





SECTION B-B





SECTION C-C


| GENERAL TOLERANCES (UNLESS SPECIFIED) | | ZHE JIANG DELI CONNECTORS CO .,LTD | | |
|---|---|---|---|---|
| .X: ± 0.25 | X° : ± 3.0° | PRODUCT NAME: DL30001(43030)-T | | TITLE: 3.0mm Pitch Wire To Board Crimp Terminal |
| .XX: ± 0.15 | .X° : ± 2.0° | | | |
| .XXX: ± 0.01 | .XX° : ± 1.0° | DR:Chen Quan Long | DATE:20.03.11 | PART NO: |
| FINISH: | | CHKD: Wu Hui | DATE:20.03.11 | SCALE: N/A / PAGE: 1/1 |
| DRAWING NO: | | APPD:Ren An De | DATE:20.03.11 | UNITS: mm / REV.: A |

| REV. | REVISION DESCRIPTION | DATE | APPD |
|---|---|---|---|
| | | | |




SECTION A-A




SECTION B-B

## NOTES

Used in DL30001-R Series Housing.
Accepts AWG #28～20 Wire Range.

Material : Phosphor Bronze .

Finish: Tin plated.

Thickness: 0.2 mm.

Green Material RoHS Compliant.

| GENERAL TOLERANCES (UNLESS SPECIFIED) | | ZHE JIANG DELI CONNECTORS CO .,LTD | | |
|---|---|---|---|---|
| .X: ± 0.25 | X° : ± 3.0° | PRODUCT NAME: DL30001(43031)-RT | | TITLE: 3.0mm Pitch Wire To Wire Crimp Terminal |
| .XX: ± 0.15 | .X° : ± 2.0° | | | |
| .XXX: ± 0.01 | .XX° : ± 1.0° | DR:Chen Quan Long | DATE:20.03.11 | PART NO: |
| FINISH: | | CHKD: Wu Hui | DATE:20.03.11 | SCALE: N/A / PAGE: 1/1 |
| DRAWING NO: | | APPD:Ren An De | DATE:20.03.11 | UNITS: mm / REV.: A |