









A1	Q01	B12	Q01
A4	US5	B9	US5
A5	CC1	B8	SH12
A6	BPI	B7	B12
A7	B01	B6	BPI
A8	SH1	B5	CC1
A9	US5	B4	US5
A12	Q01	B1	Q01
PIN	SIGNAL NAME	PIN	SIGNAL NAME

一. 原材料:

1. 塑胶:UL 94V-0型LCP黑色
2. 端子:0.15厚铜合金 C2680/C7025
3. 外壳:不锈钢 201/304
4. 卡勾:不锈钢 201/304

二. 电镀:

1. 端子:半金亮锡1u"
2. 外壳:镀镍

三. 机械性能:

插入力:5~20N
 拔出力:寿命测试前8~20N,
 寿命测试后5~20N
 耐插拔:500次/H, 10000 次
 工作温度:0℃~+50℃
 储存温度:-20℃~60℃

四. 电气性能:

额定电流:C2680/3A;C7025/5A
 接触阻抗:寿命测试前40 m Max.
 寿命测试后50 m Max
 耐高压:100V AC 1分钟 Min.
 无击穿, 无电弧
 绝缘阻抗:100 M Min.

五. 环境性能:

环 保: 产品符合ROHS要求
 盐雾测试: 温度35±2℃,
 湿度: 95—98%;
 PH值: 6.5—7.2,
 镀金区48H, 镀镍区24H

4. 焊接工艺: 推荐使用回流焊,
 本产品耐温260度, 8S



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X" ±2" X.X" ±0.5"	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: USB TYPE C 母座16P 立插 9.3H(脚距7.95)	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HYCW733-USBC16-930B	MOLD NO.
UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO: HYC-2606021614	SHEET NO. 1 OF 1