








SPECIFICATIONS:

- 1.VOLTAGE/CURRENT RATING: AC/DC 30V3.0A/PIN(power)
 - 2.WITHSTANDING VOLTAGE: 100V AC ONE MINUTE:
 - 3.INSULATION RESISTANCE:500MΩ MN:
 - 4.CONTACT RESISTANCE:50mΩ MAX:
 - 5.OPERATING TEMPERATURE RANGE:-25°C TO 85°C MATERIAL:
- MATERIAL:
- 1.TINSULATOR:LCP UL 94V-D BLACK:
 - 2.TERMINAL:COPPER ALLOY:
 - 3.METAL FITTINGS:COPPER ALLOY. PLATING:
- PLATING:
- 1.TERMINAL:GOLD PLATING
 - NICKEL 50U"MINOVER ALL:
 - 2.METAL FITTINGS:TIN 100u" MINOVER NICKEL 50UMIN

LB4407-G04P-BxR

- PACKING: R: CARRIER REEL
- 0: WITH POSITIONING POS
- 1: WITHOUT POSITIONING POSTS
- COLOR: BLACK
- PLUG
- 4PIN
- PLATING: G: GOLD FLASH
- HEIGHT: 07: 0.65H;
- 0.4 BTB
- LXWCONN BTB CONNECTOR SERIES



PCB LAYOUT (TOP VIEW)

④	修改尺寸公差	EAST_ZHOU	02/19/22'
③	新增弹高尺寸	Kavin	08/08/18'
②	新增CAP规格	Kavin	02/17/17'
①	产品料号修正	Kavin	12/01/16'
修订 SER	修改摘要 REVISION DESCRIPTION	签名 SIGNATURE	日期 DATE

GENERAL TOLERANCE
XXX ±0.30
XXX ±0.20
XXX ±0.10
ANGLES ±2°
版本 A
(REV)

		连兴旺电子(深圳)有限公司		
connectivity		LXWCONN ELECTRONICS (SHENZHEN) CO., LTD		
制图 (DR): EAST_ZHOU 2022.02.19		品名 (TITLE): 0.4 PITCH 大电流BTB PLUG		
审核 (CHKD):		料号 (PART NO): LB4407-G04P-B0R		
核准 (APPD):		比例 (SCALE): 1:1	单位 (UNITS): mm	张数 (SHEET): 1 OF 1
				图幅 (SIZE): A4