









A1	GND	B12	GND
A4	VBUS	B9	VBUS
A5	D-	B8	SBU1
A6	D+	B7	D-
A7	D-	B6	D+
A8	SBU1	B5	D-
A9	VBUS	B4	VBUS
A12	GND	B1	GND
Pin	SIGNAL NAME	Pin	SIGNAL NAME

一. 原材料:

1. 塑胶:UL 94V-0型LCP黑色
2. 端子:0.15厚铜合金 C2680/C7025
3. 外壳:不锈钢 201/304
4. 卡勾:不锈钢 201/304

二. 电镀:

1. 端子:半金亮锡1u"
2. 外壳:镀镍

三. 机械性能:

插入力:5~20N
拔出力:寿命测试前8~20N,
寿命测试后5~20N
耐插拔:500次/H, 10000 次
工作温度:0℃~+50℃
储存温度:-20℃~60℃

四. 电气性能:

额定电流: C2680/3A;C7025/5A
接触阻抗:寿命测试前40 m Max.
寿命测试后50 m Max
耐高压:100V AC 1分钟 Min.
无击穿, 无电弧
绝缘阻抗:100 M Min.

五. 环境性能:

环 保: 产品符合ROHS要求
盐雾测试: 温度35±2℃,
湿度: 95—98%;
PH值: 6.5—7.2,
镀金区48H, 镀镍区24H

4. 焊接工艺: 推荐使用回流焊,
本产品耐温260度, 8S



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X." ±2" X.X" ±0.5"	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: USB TYPE C 母座16P 立插 10.5H(脚距7.95)	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HYCW735-USBC16-105B	MOLD NO.
UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO: HYC-2606021629	
			SHEET NO. 1 OF 1	