

ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

备注:

1. 材质:

外壳: SPCC-H/T=0.3mm

端子: C2680-EH/T=0.20mm

塑胶: PBT 环保 白

2. 电镀规格:

外壳: 全部区域镀亮镍80 μ "Min. 电镀符合"RoHS"标准;

端子: 先镀30u"镍打底, 再在接触区域镀金G/F, 在焊接区域镀锡80u"Min.

3. 盐雾试验要求:

试验测试24H;

4. 电气性能:








A. 额定电流: 2.4A/CONTACT TERMINAL

B. 额定电压: 30V DC

A. 耐电压: AC 500V/1MIN.

B. 绝缘阻抗: 1000M Ω /MIN.

C. 接触阻抗: 30m Ω /Max.



COSTOMER DRAWING			LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO.,LTD				
DRAWING							
CHECK							
APPROVAL							
TOLERANCES ARE			TITLE	TYPE-A连接器4PIN弯插L13.9(卷口)	REV.	A	
30-150	±0.35	ANGLE	PART NO.	LAIL-TYPE-A-4P-01Y-WC	UNITS	mm	
10-30	±0.2						
5-10	±0.15						
0-5	±0.1						
			DWG.NO.		Projection		
±3°							