


NO.	ECN NO.	DESCRIPTION	DATE
1			

客户图



Note:

1: Material(材料):

Barrel: Brass C3604 (针管: 黄铜 C3604)

Plunger: Brass C3604 (针头: 黄铜 C3604)

Spring: SUS304 (弹簧: SUS304)

2: Plating(电镀):

Barrel: 1u' Au over 50~80u' Ni(针管: 镀金1u', 镍底50~80u'。)

Plunger: 1u' Au over 50~80u' Ni (针头: 镀金1u', 镍底50~80u'。)

Spring: No plated (弹簧: 不电镀)

3: Electrical(电气特性):

Rated Current & Voltage: DC 12V;1A (额定电压&电流: 直流12V,1A)

Contact Resistance: 50 mohm Max. at working height.

接触电阻: 最大50毫欧 (在工作高度状态下)

4: Mechanical(机械性能):

Force: 100g $\pm$ 20% at working height. (100g $\pm$ 20% 在工作高度)。

Durability: 10.000 cycles(min) (寿命: 10000次)

5: WorkTemperature(工作环境):

Withstanding Higt Temperature: 280 $^{\circ}$ C

Operational Temperature: -20 $^{\circ}$ C~ +70 $^{\circ}$ C

深圳市鑫扬泽电子有限公司										SCALE:		N/A		UNIT		mm		THE UNMARKED TOLERANCE ARE AS BELOW :				DESIGNED BY:		DWG. NO.		YZ79315045G-01					
HTTP://WWW.XYZPOGOPIN.COM										SHEET:		1 of 1		PROJECTION						LENGTH				CHECKED BY:				TITLE:		Pogo Pin	
TEL: 0755-28773277 FAX: 0755-28891353										DATE:		2014.11.04		VER.		A.0				ANGLE				APPROVED BY:							
																				X.XX ±0.05mm X.X ±0.10mm X. ±0.20mm				X.XX ±0.50° X.X ±1.00° X. ±2.00°							

