




NO.	ECN NO.	DESCRIPTION	DATE

- Note:
- 1: Material(材料) :
Housing: PA46+30%GF (胶芯: PA46)
Pin: Brass C3604 (针体: 黄铜 C3604)
 - 2: Plating(电镀) :
Pin: 3u' Au over 50~80u' Ni
(针体: 镀金3u', 镍底50~80u'.)
 - 3: Electrical(电气特性) :
Insulation Resistance: 1,000MΩ minimum.
(绝缘电阻: 1,000MΩ以上)
Dielectric Withstand Voltage: 500VAC/minute.
(抗击电压: 500VAC/minute)
 - 4: WorkTemperture(工作环境):
Withstanding Higt Temperature: 280℃
Operational Temperature: ?40℃~ ?85℃

RECOMMENDED PCB LAYOUT

深圳市鑫扬泽电子有限公司

HTTP://WWW.XYZPOGOPIN.COM

TEL:0755-28773277 FAX:0755-28891353



SCALE:	N/A	UNIT	mm
SHEET:	1 of 1	PROJECTION	
DATE:	2022.6.22	VER.	A.0

THE UNMARKED TOLERANCE ARE AS BELOW :			
LENGTH		ANGLE	
X.XX	±0.05mm	X.XX	±0.50°
X.X	±0.10mm	X.X	±1.00°
X.	±0.20mm	X.	±2.00°

DESIGNED BY:		DWG. NO.	YZ93215020T-05030-01
CHECKED BY:		TITLE:	Pogo pin 连接器
APPROVED BY:			