














RECOMMENDED PCB LAYOUT(TOP VIEW)
DEFAULT TOLERANCE ±0.05MM

CUSTOMER DRAWING		 连兴旺电子(深圳)有限公司 LXWCONN ELECTRONICS (SHENZHEN) CO., LTD			
GENERAL TOLERANCE	DESIGN	Tan	TITLE	0.5 PITCH M.2 H2.3 (E key)	
.X ±0.35	2026.05.12		PART NO.	26004-S20674BXX10R	
.XX ±0.25	CHECKED	Tan	SCALE	1:1	UNITS
.XXX ±0.15	2026.05.12		REV.	A	SHEET
ANGLE ±3°	APPROVAL	Tan	3	OF	4
SIZE	A4	2026.05.12			

RoHS Compliant
2013/95/EC





1500	9000
PCS/REEL	PCS/CARTON

CUSTOMER DRAWING		 连兴旺电子(深圳)有限公司 LXWCONN ELECTRONICS (SHENZHEN) CO., LTD				
		DESIGN Tan 2026.05.12	TITLE 0.5 PITCH M.2 H2.3 (E key)			
GENERAL TOLERANCE X ±0.35 .XX ±0.25 .XXX ±0.15 ANGLE±3°		CHECKED Tan 2026.05.12	PART NO. 26004-S20674BXX10R			
SIZE A4		APPROVAL Tan 2026.05.12	SCALE 1:1	UNITS MM	REV. A	SHEET 4 OF 4