







Stack-up Top Mount Double Sided Module
for 1.20 max top-side component height




Stack-up Top Mount Double Sided Module
for 1.35 max top-side component height



Stack-up Top Mount Double Sided Module
for 1.35 max top-side component height



HOW TO MATE AND EXTRACT
MATE: ① → ④
EXTRACT: ⑤
NOTE: Mating force will generate
from step 3 to step 4.








RECOMMENDED PCB LAYOUT(TOP VIEW)
DEFAULT TOLERANCE ±0.05MM

CUSTOMER DRAWING		LXW 连兴旺电子(深圳)有限公司 connectivity LXWCONN ELECTRONICS(SHENZHEN) CO., LTD	
GENERAL TOLERANCE .X ±0.35 .XX ±0.25 .XXX ±0.15 ANGLE±0.5°		DESIGN ZHU 2026.04.21	TITLE 0.5 PITCH M.28.5H TOPMOUNT-DOUBLE SIDED
SIZE A4		CHECKED	PART NO. 26007-S2XXX4BXX00R
APPROVAL		SCALE 1:1	UNITS MM
		REV. A	SHEET 2 OF 4

RoHS
Compliant
2013/95/EC






Assembly stack height schematic diagram



RoHS
Compliant
2013/95/EC



CUSTOMER DRAWING		 连兴旺电子(深圳)有限公司 connectivity LXWCONN ELECTRONICS (SHENZHEN) CO., LTD				
GENERAL TOLERANCE .X ±0.35 .XX ±0.25 .XXX ±0.15 ANGLE±0.5°		DESIGN ZHU 2026.04.21	TITLE 0.5 PITCH M.28.5H TOPMOUNT-DOUBLE SIDED			
CHECKED		PART NO. 26007-S2XXX4BXX00R				
SIZE A4		APPROVAL	SCALE 1:1	UNITS MM	REV. A	SHEET 3 OF 4



550	3300
PCS/REEL	PCS/CARTON

RoHS
Compliant
2013/95/EC



CUSTOMER DRAWING		 连兴旺电子(深圳)有限公司 connectivity LXWCONN ELECTRONICS(SHENZHEN) CO., LTD				
GENERAL TOLERANCE X ±0.35 XX ±0.25 XXX ±0.15 ANGLE ±0.5°		DESIGN ZHU 2026.04.21	TITLE 0.5 PITCH M.28.5H TOPMOUNT-DOUBLE SIDED 包装图			
CHECKED		PART NO. 26007-S2XXX4BXX00R				
SIZE A4		APPROVAL	SCALE 1:1	UNITS MM	REV. A	SHEET 4 OF 4