






| NO. | ECN NO. | DESCRIPTION | DATE |
|-----|---------|-------------|------|
|     |         |             |      |



RECOMMENDED PCB LAYOUT



Note:

- Material(材料):  
Housing: PA46+30%GF (胶芯: PA46)  
Pin: Brass C3604 (针体: 黄铜 C3604)
- Plating(电镀):  
Pin: 3u' Au over 50~80u' Ni (针体: 镀金3u', 镍底50~80u'.)
- Electrical(电气特性):  
Insulation Resistance: 1,000MΩ minimum. (绝缘电阻: 1,000MΩ以上)  
Dielectric Withstand Voltage: 500VAC/minute. (抗击电压: 500VAC/minute)
- WorkTemperture(工作环境):  
Withstanding Higt Temperature: 280℃  
Operational Temperature: ?40℃~ ?85℃

深圳市鑫扬泽电子有限公司

HTTP://WWW.XYZPOGOPIN.COM

TEL:0755-28773277 FAX:0755-28891353



|        |           |            |           |
|--------|-----------|------------|-----------|
| SCALE: | N/A       | UNIT       | mm        |
| SHEET: | 1 of 1    | PROJECTION | 1st Angle |
| DATE:  | 2022.2.15 | VER.       | D.0       |

THE UNMARKED TOLERANCE ARE AS BELOW :

| LENGTH       | ANGLE       |
|--------------|-------------|
| X.XX ±0.05mm | X.XX ±0.50° |
| X.X ±0.10mm  | X.X ±1.00°  |
| X. ±0.20mm   | X. ±2.00°   |

|              |  |          |                      |
|--------------|--|----------|----------------------|
| DESIGNED BY: |  | DWG. NO. | YZ93215020T-03025-01 |
| CHECKED BY:  |  | TITLE:   | Pogo pin连接器          |
| APPROVED BY: |  |          |                      |