

ROHS









REV.	ECN NO.	DESCRIPTION	DRAW	DATE

SPECIFICATION:

- MATERIAL & FINISH:SEE THE LIST;
- PLATING SPECIFICATION:
 - CONTACTS:
Ni 50u" MIN. UNDER PLATED OVER
ALL.
Au PLATED ON THE MATING AREA OF CONTACT.
Sn PLATED ON THE SOLDER AREA.
 - SHELL:Ni 30u" MIN. UNDER PLATED OVER ALL.
 - MID PLATE:CLEAR ONLY
- MECHANICAL:
 - MATING FORCE:0.5~2.0kgf;
 - UNMATING FORCE:0.8~2.0kgf.
0.6~2.0kgf AFTER DURABILITY

TEST;

- DURABILITY:10000 CYCLES;
- ELECTRICAL:
 - CURRENT RATING:3A/5A Max;
 - VOLTAGE RATING:30V Max;
 - DIELECTRIC WITHSTANDING
VOLTAGE:100VAc;
 - CONTACT RESISTANCE:40mΩ Ohms
Max.;
 - INSULATION RESISTANCE:100M
Ohms Min.;
- ENVIRONMENTAL:
 - OPERATING
TEMPERATURE:-25°C~+85°C;
 - WETTING
TEMPERATURE:265±5°C,5±0.5s



PIN DEFINE TABLE			
PIN	SIGNAL	PIN	SIGNAL
A12	GND	B1	GND
A11		B2	
A10		B3	
A9	VBUS	B4	VBUS
A8		B5	CC2
A7	D-	B6	D+
A6	D+	B7	D-
A5	CC1	B8	
A4	VBUS	B9	VBUS
A3		B10	
A2		B11	
A1	GND	B12	GND



NO.	PART NAME	Q' TY	MATERIAL	FINISH		
4	Shell	1	Stainless Steel, T=0.30mm	30u"Ni Min.		
3	GroundBar	1	Stainless Steel, T=0.15mm	No Plating		
2	Contact	14	Copper Alloy, T=0.15mm	Au/Sn/Ni-Plated		
1	Housing	1	High temperature plastic	UL94 V-0, Black		
COSTOMER DRAWING		 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO., LTD				
DRAWING						
CHECK						
APPROVAL						
TOLERANCES ARE		TITLE	TYPE-C连接器14PIN直插H10.0	REV.	A	
30-150	±0.35	ANGLE	PART NO.	LAIL-TYPE-C-14PIN-01Y-ZC	UNITS	mm
10-30	±0.2					
5-10	±0.15					
0-5	±0.1					
		±3°	DWG.NO.		Projection	

SHENZHEN LAILIAN ELECTRONICS CO., LTD

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

说明:

- 1.每卷前后各空16PCS,尾部用美纹胶纸封住;
- 2.将产品放满盘后,再卷一圈保护带,用美纹胶纸将其封住,并贴上1Pcs物料标签;
- 3.每10卷盘一叠共5000Pcs并装入1个外箱内;
- 4.在搬运过程中要轻拿轻放;
- 5.在运输中不可堆放过多(1.8M最高),不可重压;
- 6.跌落测试条件:
成品箱从1.2米高度自由落体(一角三棱六面):
a.产品不可跑出下带凹槽;
b.产品不可有摔伤,变形;
c.内包装材料不可严重破损.



COSTOMER DRAWING				 深圳市莱联电子有限公司									
DRAWING				SHENZHEN LAILIAN ELECTRONICS CO., LTD									
CHECK													
APPROVAL													
TOLERANCES ARE				TITLE		TYPE-C连接器14PIN直插H10.0		REV.		A			
30-150		±0.35		ANGLE		PART NO.		LAIL-TYPE-C-14PIN-01Y-ZC		UNITS		mm	
10-30		±0.2											
5-10		±0.15											
0-5		±0.1											
						DWG.NO.				Projection			