









RECOMMENDED P.C.B. LAYOUT
TOLERANCE UNSPECIFIED ±0.05mm

A1	C00	B12	C00
A4	VBS	B9	VBS
A5	CC1		
A6	DP1	B7	DP2
A7	DP1	B6	DP2
		B5	CC2
A9	VBS	B4	VBS
A12	C00	B1	C00
PIN	STANDARD NAME	PIN	STANDARD NAME

一. 原材料:

1. 塑胶:UL 94V-0型LCP黑色
2. 端子:0.15厚铜合金 C2680/C7025
3. 外壳:不锈钢 201/304
4. 卡勾:不锈钢 201/304

二. 电镀:

1. 端子:半光亮锡1u"
2. 外壳:镀镍

三. 机械性能:

插入力:5~20N

拔出力:寿命测试前8~20N,

寿命测试后5~20N

耐插拔:500次/H, 10000 次

工作温度:0℃~+50℃

储存温度:-20℃~60℃

四. 电气性能:

额定电流: C2680/3A;C7025/5A

接触阻抗:寿命测试前40 m Max.

寿命测试后50 m Max

耐高压:100V AC 1分钟 Min.

无击穿, 无电弧

绝缘阻抗:100 M Min.

五. 环境性能:

环 保: 产品符合ROHS要求

盐雾测试: 温度35±2℃,

湿度: 95—98%;

PH值: 6.5—7.2,

镀金区48H, 镀镍区24H

4. 焊接工艺:

推荐使用回流焊,

本产品耐温260度, 8S



深圳市华宇创精密电子有限公司


TOLERANCE:

X.X ±0.30

X.XX ±0.25

X.XXX ±0.15

X' ±2" X.X' ±0.5"



UNIT: mm [inch]

SCALE:1:1

SIZE: A4

DRAWN BY :

陈一鸣

DATE :

2014-02-23

PART NAME:

USB TYPE C 母座14P 180度插板 鱼叉脚 10.0H

CHECKED BY:

马跃

DATE :

2014-02-23

PART NO.

HYCW727-USBC14-100B

APPROVED BY:

邱敏

DATE :

2014-02-23

DRAW NO:

HYC-2606021440

SHEET NO.

1 OF 1