










RECOMMENDED P.C.B. LAYOUT (T:1.00mm)
TOLERANCE UNSPECIFIED $\pm 0.05\text{mm}$
SCALE: 2:1

A1	GND	B12	GND
A4	VBUS	B9	VBUS
A5	CC1	B8	SR02
A6	DP1	B7	DP2
A7	DM1	B6	DP2
A8	SR01	B5	CC2
A9	VBUS	B4	VBUS
A12	GND	B1	GND
PLN	SIGNAL NAME	PLN	SIGNAL NAME

一. 原材料:

1. 塑胶: UL 94V-0型LCP黑色
2. 端子: 0.15厚铜合金 C2680/C7025
3. 外壳: 不锈钢 201/304
4. 卡勾: 不锈钢 201/304

二. 电镀:

1. 端子: 半金亮锡1u"
2. 外壳: 镀镍

三. 机械性能:

插入力: 5~20N
拔出力: 寿命测试前8~20N,
寿命测试后5~20N
耐插拔: 500次/H, 10000 次
工作温度: $0^{\circ}\text{C} \sim +50^{\circ}\text{C}$
储存温度: $-20^{\circ}\text{C} \sim 60^{\circ}\text{C}$

四. 电气性能:

额定电流: C2680/3A; C7025/5A
接触阻抗: 寿命测试前40m Ω
寿命测试后50 m Ω
耐高压: 100V AC 1分钟 Min.
无击穿, 无电弧
绝缘阻抗: 100 M Ω Min.

五. 环境性能:

环 保: 产品符合ROHS要求
盐雾测试: 温度 $35 \pm 2^{\circ}\text{C}$,
湿度: 95—98%;
PH值: 6.5—7.2,
镀金区48H, 镀镍区24H

4. 焊接工艺: 推荐使用回流焊,
本产品耐温260度, 8S



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ± 0.30 X.XX ± 0.25 X.XXX ± 0.15 X." $\pm 2^{\circ}$ X.X" $\pm 0.5^{\circ}$	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: USB TYPE C 母座16P 立贴5.5H	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HYCW717-USBC16-550B	MOLD NO.
UNIT: mm [inch] SCALE: 1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO: HYC-2605291501	SHEET NO. 1 OF 1