



客户图



技术要求:

1. 材料:黄铜C3602.
2. 不允许有批锋,毛刺;切断点最大不超过0.05mm.
3. 表面处理:不电镀.

深圳市鑫探技术有限公司

HTTP://WWW.XYZPOGOPIN.COM

TEL:0755-28773277 FAX:0755-28891353



SCALE:	N/A	UNIT	mm
SHEET:	1 of 1	PROJECTION	
DATE:	2024.12.20	VER.	D.0

THE UNMARKED TOLERANCE ARE AS BELOW :

LENGTH		ANGLE	
X.XX	±0.05mm	X.XX	±0.50°
X.X	±0.10mm	X.X	±1.00°
X.	±0.20mm	X.	±2.00°

DESIGNED BY:		DWG. NO.	YZB0104-23068-01
CHECKED BY:		TITLE:	Pogo pin连接器
APPROVED BY:			