





客户图



RECOMMENDED PCB LAYOUT



Note:

1: Material(材料) :

Housing: PA46+30%GF (胶芯: PA46)

Pin: Brass C3604 (针体: 黄铜 C3604)

2: Plating(电镀) :

Pin: 5u' Au over 50~80u' Ni

针体: 镀金5u', 镍底50~80u'。

3: Electrical(电气特性) :

Insulation Resistance: 1,000M Ω minimum.

(绝缘电阻: 1,000M Ω 以上)

Dielectric Withstand Voltage: 500VAC/minute.

(抗击电压: 500VAC/minute)

4: WorkTemperture(工作环境):

Withstanding Higt Temperature: 280°C

Operational Temperature: - 40°C ~ + 85°C

深圳市鑫探技术有限公司

[HTTP://WWW.XYZPOGOPIN.COM](http://www.xyzpogopin.com)

TEL:0755-28773277 FAX:0755-28891353



SCALE: N/A

UNIT

mm

THE UNMARKED TOLERANCE ARE AS BELOW :

LENGTH

ANGLE

X.XX ± 0.05 mm
X.X ± 0.10 mm
X. ± 0.20 mm

X.XX $\pm 0.50^\circ$
X.X $\pm 1.00^\circ$
X. $\pm 2.00^\circ$

DESIGNED BY:

DWG. NO.

YZ93215020T-02025-03

CHECKED BY:

APPROVED BY:

TITLE:

Pogo pin 连接器