








ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE



NOTES:
1.MECHANICAL:
MATING: 35N MAX.
WITHDRAWAL: COPPER ALLOY 10N MIN.
SPCC 5N MIN
DURABILITY: 1500 CYCLES MIN.
2.ELECTRICAL:
CURRENT: 1.8A MAX For Pin1 And Pin4 and
0.25A for all the other pins
VOLTAGE: 30V MAX
WITHSTANDING VOLTAGE: 100V AC
CONTACT RESISTANCE: 30 mΩ Maximum.
Initial for VBUS and GND contacts
50 mΩ MAX
INSULATION RESISTANCE: 100MΩ MIN
3.ENVIRONMENTAL
TEMPERATURE RANGE -25°C ~ +85°C



SECTION:B-B



P.C.B LAYOUT(±0.05)



SECTION:A-A

COSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO.,LTD				
DRAWING		TITLE		TYPE-B连接器9PIN卧贴L18.35(平口)	REV.	A
CHECK						
APPROVAL		PART NO.		LAIL-TYPE-B-9P-01Y-WC	UNITS	mm
TOLERANCES ARE						
30-150	±0.35	ANGLE	DWG.NO.		Projection	
10-30	±0.2					
5-10	±0.15					
0-5	±0.1					
			±3°			