





| NO. | ECN NO. | DESCRIPTION | DATE |
|-----|---------|-------------|------|
|     |         |             |      |



RECOMMENDED PCB LAYOUT

Note:

- Material (材料) :  
Housing: PA46+30%GF (胶芯: PA46)  
Pin: Brass C3604 (针体: 黄铜 C3604)
- Plating (电镀) :  
Pin: 3u' Au over 50~80u' Ni  
针体: 镀金3u', 镍底50~80u'.
- Electrical (电气特性) :  
Insulation Resistance: 1,000M $\Omega$  minimum.  
(绝缘电阻: 1,000M $\Omega$  以上)  
Dielectric Withstand Voltage: 500VAC/minute.  
(抗击电压: 500VAC/minute)
- WorkTemperture (工作环境):  
Withstanding Higt Temperature: 280 $^{\circ}$ C  
Operational Temperature: - 40 $^{\circ}$ C ~ + 85 $^{\circ}$ C

深圳市鑫扬泽电子有限公司

HTTP://WWW.XYZPOGOPIN.COM

TEL:0755-28773277 FAX:0755-28891353



|        |            |            |     |
|--------|------------|------------|-----|
| SCALE: | N/A        | UNIT       | mm  |
| SHEET: | 1 of 1     | PROJECTION |     |
| DATE:  | 2016.01.25 | VER.       | D.0 |

| THE UNMARKED TOLERANCE ARE AS BELOW : |         |       |        |
|---------------------------------------|---------|-------|--------|
| LENGTH                                |         | ANGLE |        |
| X.XX                                  | ±0.05mm | X.XX  | ±0.50° |
| X.X                                   | ±0.10mm | X.X   | ±1.00° |
| X.                                    | ±0.20mm | X.    | ±2.00° |

|              |  |          |                      |
|--------------|--|----------|----------------------|
| DESIGNED BY: |  | DWG. NO. | YZ92015035T-02025-02 |
| CHECKED BY:  |  | TITLE:   | Pogo pin 连接器         |
| APPROVED BY: |  |          |                      |