




NOTES:


- MATERIAL SPECIFICATION:
1-1. HOUSING: LCP+40%GF, UL94V-0, COLOR: BLACK.
1-2. CONTACT: COPPER ALLOY.
1-3. SMT TAB: S50C.
- PLATING SPECIFICATION:
2-1. CONTACT:
50u" MIN. NICKEL UNDER PLATING OVER ALL.
G/F PLATING ON SOLDER AREA.
GOLD PLATING ON CONTACT AREA: SEE TABLE
2-2. SMT TAB:
50u" MIN. NICKEL UNDER PLATING OVER ALL.
80u" MIN. MATTE TIN PLATING ON SOLDER AREA.
- HF COMPLIANT, ROHS COMPLIANT.
- DATE CODE: XXXXXX
DAY
WEEK
YEAR
- MECHANICAL PERFORMANCE:
5-1. DURABILITY: SEE TABLE
- ELECTRICAL PERFORMANCE:
6-1. CURRENT: 0.5A PER PIN.
6-2. LLCR: INITIAL 55mΩ MAX.; FINAL ΔLLCR=20mΩ MAX..
- IR REFLOW:
THE TEMPERATURE SHALL BE 260±5°C MAINTAINING 10±1 SECONDS.







PART NO.	CONTACT PLATING	DURABILITY
26004-S20674BG811R	30u" MIN. GOLD	60 CYCLES.
26004-S20674BGF11R	1~3u" MIN. GOLD	25 CYCLES.
26004-S20674BG611R	10u" MIN. GOLD	25 CYCLES.
26004-S20674BG511R	5u" MIN. GOLD	25 CYCLES.

CUSTOMER DRAWING		连兴旺电子(深圳)有限公司 connectivity LXWCONN ELECTRONICS (SHENZHEN) CO., LTD			
GENERAL TOLERANCE .X ±0.35 .XX ±0.25 .XXX ±0.15 ANGLE ±3°	DESIGN Tan 2026.05.12	TITLE 0.5Pitch 67pin M.2 H3.2 (KEYE)	PART NO. 26004-S20674BXX11R		
SIZE A4	CHECKED Tan 2026.05.12	APPROVAL Tan 2026.05.12	SCALE 1:1	UNITS MM	REV. A
				SHEET 1 OF 4	

RoHS
Compliant
2013/95/EC











RECOMMENDED PCB LAYOUT(TOP VIEW)
DEFAULT TOLERANCE ±0.05MM

CUSTOMER DRAWING		LXW 连兴旺电子(深圳)有限公司 connectivity LXWCONN ELECTRONICS (SHENZHEN) CO., LTD			
GENERAL TOLERANCE .X ±0.35 .XX ±0.25 .XXX ±0.15 ANGLE ±3°		DESIGN Tan 2026.05.12	TITLE 0.5Pitch 67pin M.2 H3.2 (KEYE)		
SIZE A4		CHECKED Tan 2026.05.12	PART NO. 26004-S20674BXX11R		
APPROVAL Tan 2026.05.12		SCALE 1:1	UNITS MM	REV. A	SHEET 3 OF 4



1200	9600
PCS/REEL	PCS/CARTON

CUSTOMER DRAWING	 连兴旺电子(深圳)有限公司 LXWCONN ELECTRONICS (SHENZHEN) CO., LTD	
	DESIGN Tan 2026.05.12	TITLE 0.5Pitch 67pin M.2 H3.2 (KEYE)
GENERAL TOLERANCE .X ± 0.35 .XX ± 0.25 .XXX ± 0.15 ANGLE $\pm 3^{\circ}$	CHECKED Tan 2026.05.12	PART NO. 26004-S20674BXX11R
SIZE A4	APPROVAL Tan 2026.05.12	SCALE 1:1
		UNITS MM
		REV. A
		SHEET 4 OF 4

RoHS Compliant
2013/95/EC

