





ROHS



备注

1. 材质

端子:C5191 R-EH;T=0.25mm.
胶芯:PBT白色+30% G.F,UL 94V-0.
壳子:铁壳/铜壳镀镍; T=0.30mm.
后盖:铁壳镀镍; T=0.30mm.

2. 机械性能:

插入力:35N Max(铁壳仅参考).
拔出力:10N Min(铁壳仅参考).
寿命:1500 Cycles Min(铁壳仅参考).

3. 电气性能:


额定电流:1.5A.
额定电压:30V AC(rms).
耐电压:500V AC For One Minute.
接触电阻:30mΩ Max.
绝缘电阻:1000MΩ Min.

4. 电镀:

端子:全部镍底50u"Min/接触区域镀金1u"/焊接区域电镀亮锡100u"Min.
外壳铁壳镀铜底80u"Min, 镀镍100u"Min.
外壳铜壳镀镍100u"Min.

5. 环境测试:

温度范围:-55° C To +85° C.



COSTOMER DRAWING			LAILIAN 深圳市莱联电子有限公司				
DRAWING			SHENZHEN LAILIAN ELECTRONICS CO.,LTD				
CHECK							
APPROVAL							
TOLERANCES ARE			TITLE		TYPE-B连接器4PIN弯插L16.4(平口)	REV.	A
ANGLE ±3°			PART NO.		LAIL-TYPE-B-4P-01Y-WC	UNITS	mm
			DWG.NO.			Projection	