







标记
MARKECN编号/变更内容
ECN NO/DEFINITION修改
REVISE日期
DATE核准
APPROVE

编号



尺寸 (mm)

	A	B	C
2X04A	7.50	15.00	11.50
2X05A	10.00	17.50	14.00
2X06A	12.50	20.00	16.50
2X07A	15.00	22.50	19.00
2X08A	17.50	25.00	21.50
2X09A	20.00	27.50	24.00
2X10A	22.50	30.00	26.50
2X11A	25.00	32.50	29.00
2X12A	27.50	35.00	31.50
2X13A	30.00	37.50	34.00
2X14A	32.50	40.00	36.50
2X15A	35.00	42.50	39.00
2X16A	37.50	45.00	41.50



SPECIFICATIONS

1. Current Rating: 3A AC, DC
2. Voltage Rating: 250V AC, DC
3. Temperature Range: -25°C ~ +85°C
4. Contact Resistance: 20mΩ Max
5. Insulation Resistance: 1000MΩ Min
6. Withstanding Voltage: 1000V AC/minute
7. Material: Wafer PA46
PIN Brass Tin-plated



PCB LAYOUT

2	插针	铜	镀锡	
1	底座	PA46	米色	
序号	品名	材质	电镀/颜色	备注



深圳市虹成电子有限公司

品名 TITLE	针座
料号 PART NO	HC-XAD2.54-2x6A

GENERAL TOLERANCES
(UNLESS SPECIFIED)比例
SCALE

1:1

X±0.25 X'±2"

单位
UNIT

MM

.X±0.20 .X'±1"

张数
PART NO

1 OF 1

.XX±0.15 .XX'±0.5"

审核
CHECKED

夏操云

.XXX±0.10 .XXX'±0.5"

版本
REV

A

制图
DRAW

AhYe

批准
APPROVE

赵亮亮

