






标记
MARKPCN编号/变更内容
PCN NO/DEFINITION修改
REVISE日期
DATE核准
APPROVE

PIN	尺寸 (mm)		
	A	B	C
2*04AW	7.50	15.00	11.50
2*05AW	10.00	17.50	14.00
2*06AW	12.50	20.00	16.50
2*07AW	15.00	22.50	19.00
2*08AW	17.50	25.00	21.50
2*09AW	20.00	27.50	24.00
2*10AW	22.50	30.00	26.50
2*11AW	25.00	32.50	29.00
2*12AW	27.50	35.00	31.50
2*13AW	30.00	37.50	34.00
2*14AW	32.50	40.00	36.50
2*15AW	35.00	42.50	39.00
2*16AW	37.50	45.00	41.50





SPECIFICATIONS



- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25℃~+85℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000MΩ Min
- 6、Withstanding Voltang: 1000V AC/minute
- 7、Material: Wafer PA46
PIN Brass Tin-plated




2*4-2*6A



2*7-2*8A




2*9-2*20A



PCB LAYOUT

2	插针	铜	镀锡	
1	基座	PA46	米色	
序号	品名	材质	电镀/颜色	备注

		深圳市虹成电子有限公司		品名 TITLE	针座
				料号 PART NO	HC-XAD2.54-2x5AW
一般公差 TOLERANCE		比列 SCALE	1:1		
X±0.25	X°±2°	单位 UNIT	MM	制图 DRAW	AhYe
X±0.25	X°±1°	张数 PART NO	1 OF 1	审核 CHECKED	夏操云
XX±0.15	XX°±0.5°	版本 REV	A	批准 APPROVE	赵亮亮
XXX±0.10	XXX°±0.5°				