











标记
MARKPCN编号/变更内容
PCN NO/DEFINITION修改
REVISE日期
DATE核准
APPROVE

PIN	尺寸 (mm)		
	A	B	C
2*04AW	7.50	15.00	11.50
2*05AW	10.00	17.50	14.00
2*06AW	12.50	20.00	16.50
2*07AW	15.00	22.50	19.00
2*08AW	17.50	25.00	21.50
2*09AW	20.00	27.50	24.00
2*10AW	22.50	30.00	26.50
2*11AW	25.00	32.50	29.00
2*12AW	27.50	35.00	31.50
2*13AW	30.00	37.50	34.00
2*14AW	32.50	40.00	36.50
2*15AW	35.00	42.50	39.00
2*16AW	37.50	45.00	41.50



SPECIFICATIONS


- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25℃~+85℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000MΩ Min
- 6、Withstanding Voltang: 1000V AC/minute
- 7、Material: Wafer PA46
PIN Brass Tin-plated



2*4-2*6A

2*7-2*8A

2*9-2*20A



PCB LAYOUT

2	插针	铜	镀锡	
1	基座	PA46	米色	
序号	品名	材质	电镀/颜色	备注

 深圳市虹成电子有限公司		品 名 TITLE		针 座		
		料 号 PART NO		HC-XAD2. 54-2x4AW		
一般公差 TOLERANCE		比 列 SCALE	1 : 1			
X±0.25 X°±2°		单 位 UNIT	MM			
X±0.25 X°±1°		张 数 PART NO	1 OF 1	制 图 DRAW	AhYe	
XX±0.15 XX°±0.5°		版 本 REV	A	审 核 CHECKED	夏操云	
XXX±0.10 XXX°±0.5°				批 准 APPROVE	赵亮亮	

