





1. Spacing: 1.25
2. Voltage Rating: 125V AC DC
3. Current Rating: 1A AC, DC
4. Insulation Resistance: 100M Ω Min
5. Contact Resistance: 20m Ω Max
6. Withstanding voltage: 500V AC 1/Minute
7. Temperatuer Range: -25 $^{\circ}$ C ~+ 85 $^{\circ}$ C

<i>Part No</i>	<i>Pin</i>	<i>A</i>	<i>B</i>	<i>C</i>
<i>HMT-GH1. 25-WT2P</i>	<i>2</i>	<i>1. 25</i>	<i>5. 75</i>	<i>3. 75</i>
<i>HMT-GH1. 25-WT3P</i>	<i>3</i>	<i>2. 50</i>	<i>7. 00</i>	<i>5. 00</i>
<i>HMT-GH1. 25-WT4P</i>	<i>4</i>	<i>3. 75</i>	<i>8. 25</i>	<i>6. 25</i>
<i>HMT-GH1. 25-WT5P</i>	<i>5</i>	<i>5. 00</i>	<i>9. 50</i>	<i>7. 50</i>
<i>HMT-GH1. 25-WT6P</i>	<i>6</i>	<i>6. 25</i>	<i>10. 75</i>	<i>8. 75</i>
<i>HMT-GH1. 25-WT7P</i>	<i>7</i>	<i>7. 50</i>	<i>12. 00</i>	<i>10. 00</i>
<i>HMT-GH1. 25-WT8P</i>	<i>8</i>	<i>8. 75</i>	<i>13. 25</i>	<i>11. 25</i>
<i>HMT-GH1. 25-WT9P</i>	<i>9</i>	<i>10. 00</i>	<i>14. 50</i>	<i>12. 50</i>
<i>HMT-GH1. 25-WT10P</i>	<i>10</i>	<i>11. 25</i>	<i>15. 75</i>	<i>13. 75</i>
<i>HMT-GH1. 25-WT11P</i>	<i>11</i>	<i>12. 50</i>	<i>17. 00</i>	<i>15. 00</i>
<i>HMT-GH1. 25-WT12P</i>	<i>12</i>	<i>13. 75</i>	<i>18. 25</i>	<i>16. 25</i>
<i>HMT-GH1. 25-WT13P</i>	<i>13</i>	<i>15. 00</i>	<i>19. 50</i>	<i>17. 50</i>
<i>HMT-GH1. 25-WT14P</i>	<i>14</i>	<i>16. 25</i>	<i>20. 75</i>	<i>18. 75</i>
<i>HMT-GH1. 25-WT15P</i>	<i>15</i>	<i>17. 50</i>	<i>22. 00</i>	<i>20. 00</i>
<i>HMT-GH1. 25-WT16P</i>	<i>16</i>	<i>18. 75</i>	<i>23. 25</i>	<i>21. 25</i>

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 HMTCONN Shenzhen Huamingtong Electronics Co., Ltd			
X.X ±0.30	X.° ±5°	PART NO.	TITLE:		
.XX ±0.20	X.X° ±1°	HMT-GH1.25-WTNP	WAFER GH1.25 卧贴带扣		
.XXX ±0.10	X.XX° ±0.5°	DESIGN: James	CUSTOMER	SIZE	UNITS
MANUFACTURE DWG		CHED: Talen		A4	MM
		APPD: Sophia		SCALE	SHEET
				N:A	1/1