





技术指标:

- 1. 额定电流 :0.5A
- 2. 温度范围 : -40~85℃
- 3. 额定电压 :50V, AC/DC (等效)
- 4. 接触电阻 : ≤0.03Ω
- 5. 绝缘电阻 : ≥500MΩ

| Part No         | Pin  | A          | B               | C          |
|-----------------|------|------------|-----------------|------------|
| FC10A-LZH25-4P  | 4    | 3.00       | 5.15            | 11.00      |
| FC10A-LZH25-5P  | 5    | 4.00       | 6.15            | 12.00      |
| FC10A-LZH25-6P  | 6    | 5.00       | 7.15            | 13.00      |
| FC10A-LZH25-7P  | 7    | 6.00       | 8.15            | 14.00      |
| FC10A-LZH25-8P  | 8    | 7.00       | 9.15            | 15.00      |
| FC10A-LZH25-9P  | 9    | 8.00       | 10.15           | 16.00      |
| FC10A-LZH25-10P | 10   | 9.00       | 11.15           | 17.00      |
| FC10A-LZH25-11P | 11   | 10.00      | 12.15           | 18.00      |
| FC10A-LZH25-12P | 12   | 11.00      | 13.15           | 19.00      |
| .....           | .... | ...        | .....           | .....      |
| FC10A-LZH25-36P | 36   | (36-1)*1.0 | (36+1)*1.0+0.15 | (36+7)*1.0 |

| 序号 | 品名       | 材质             |
|----|----------|----------------|
| 1  | 1.0A胶芯   | LCP UL94V-0 本色 |
| 2  | 1.0A立贴端子 | 磷青铜 / 表面镀锡     |
| 3  | 1.0A锁条   | LCP UL94V-0 黑色 |
| 4  | 1.0A焊片   | 黄铜 / 表面镀锡      |

|                                        |     |                                                                                                                                                 |                                                                                       |              |
|----------------------------------------|-----|-------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|--------------|
| GENERAL TOLERANCES<br>UNLESS SPECIFIED |     |  深圳市华明通电子有限公司<br>Shenzhen Huamingtong Electronics Co., Ltd |                                                                                       |              |
| X.±0.15                                | ±1° | PART NO.<br>FC10A-LZH25-NP                                                                                                                      | TITLE:<br>1.0-A拉拔立贴 (H:2.5)                                                           |              |
| .X±0.10                                |     |                                                                                                                                                 |                                                                                       |              |
| .XX±0.05                               |     | DESIGN: James                                                                                                                                   | CUSTOMER                                                                              | SIZE<br>A4   |
| MANUFACTURE DWG                        |     | CHED: Talen                                                                                                                                     |                                                                                       | UNITS<br>MM  |
|                                        |     | APPD: Sophia                                                                                                                                    |  | SCALE<br>N:A |
|                                        |     |                                                                                                                                                 |                                                                                       | SHEET<br>1/1 |